On-Q
20-inch Enclosure, No Cover
Part No. EN2080

This 20"" enclosure features universal On-Q bay-style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for

Features & Benefits

- Includes five openings on the top of the enclosure with knockouts
- Flush and surface installation
- Patented mounting system offers versatile module mounting options
- Includes self-adhesive cable identification table
- Drywall depth indicators
- Mounting tabs provide correct flush-mount position for standard installations
- Literature pouch included for dealer information
- Made in the USA

Specifications

General Info

Product Line	On-Q	Color	White
UPC Number	804428023104	Country Of Origin	United States
Material	Steel	Application Sector	Residential
Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS	Type	Enclosure

Dimensions

Product Width US	14.25 in	Product Depth US	3.6 in
Product Height US	20.0 in	Enclosure Size	20 in

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes

Additional Information

RoHS Compliant	Yes

Technical Information

Thickness	0.1 in	Frame	Cold Rolled Steel

On-Q
20-inch Enclosure, No Cover
Part No. EN2080

This 20"" enclosure features universal On-Q bay-style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for

Features & Benefits

- Includes five openings on the top of the enclosure with knockouts
- Flush and surface installation
- Patented mounting system offers versatile module mounting options
- Includes self-adhesive cable identification table
- Drywall depth indicators
- Mounting tabs provide correct flush-mount position for standard installations
- Literature pouch included for dealer information
- Made in the USA

Specifications

General Info

Product Line	On-Q	Color	White
UPC Number	804428023104	Country Of Origin	United States
Material	Steel	Application Sector	Residential
Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS	Type	Enclosure

Dimensions

Product Width US	14.25 in	Product Depth US	3.6 in
Product Height US	20.0 in	Enclosure Size	20 in

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes

Additional Information

RoHS Compliant	Yes

Technical Information

Thickness	0.1 in	Frame	Cold Rolled Steel