

Eaton ENP5151

Catalog Number: ENP5151

Eaton Crouse-Hinds series Ark-Gard ENP plug, 15A, 50-400 Hz, Copper-free aluminum, 5-15P, 125 Vac

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Ark-Gard ENP plug	ENP5151
	UPC
	782274310855
Product Length/Depth	Product Height
3.91 in	1.6 in
Product Width	Product Weight
1.6 in	0.3 lb



Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

7

9

12

Product specifications

Amperage Rating

15A

Voltage rating

125 Vac

NEMA configuration

5-15P

Material

Copper-free aluminum

Frequency rating

50-400 Hz

Resources

3D CAD drawing package

[Eaton Crouse-Hinds ENP5151 3D drawing](#)

Catalogs

[Ark-Gard ENP Explosionproof NEMA Locking Devices catalog page](#)

Certification reports

[Ark-Gard ENP, ENR, ENC Explosionproof NEMA Locking Devices UL certification - ENR and ENP](#)

[Ark-Gard ENP, ENR, ENC Explosionproof NEMA Locking Devices Canadian certification - ENR and ENP](#)

Installation instructions

[IF 344 - Ark-Gard ENR Receptacles ENP Model M97 Plugs](#)

Specifications and datasheets

[Eaton Specification Sheet - ENP5151](#)

Reserved.

owners.

[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)