

# Eaton ENP6202

Catalog Number: ENP6202

Eaton Crouse-Hinds series Ark-Gard ENP plug, 20A, 50-400 Hz, Copper-free aluminum, 6-20P, 250 Vac

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Ark-Gard ENP plug	ENP6202
	UPC
	782274310886
Product Length/Depth	Product Height
3.91 in	1.6 in
Product Width	Product Weight
1.6 in	0.3 lb

## Certifications and compliances

### Area classification

Hazardous/Classified Locations

### Standards type

NEC/CEC

### NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

### NEMA Rating

3

7

9

12

## Product specifications

### Amperage Rating

20A

### Voltage rating

250 Vac

### NEMA configuration

6-20P

### Material

Copper-free aluminum

### Frequency rating

50-400 Hz

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds ENP6202 3D drawing](#)

### Catalogs

[Ark-Gard ENP Explosionproof NEMA Locking Devices catalog page](#)

### Certification reports

[Ark-Gard ENP, ENR, ENC Explosionproof NEMA Locking Devices UL certification - ENR and ENP](#)

[Ark-Gard ENP, ENR, ENC Explosionproof NEMA Locking Devices Canadian certification - ENR and ENP](#)

### Installation instructions

[IF 344 - Ark-Gard ENR Receptacles ENP Model M97 Plugs](#)

### Specifications and datasheets

[Eaton Specification Sheet - ENP6202](#)

---

Reserved.

owners.

[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)