

Eaton ER53030UD

Catalog Number: ER53030UD

Eaton enclosed rotary disconnect switch, 30 A, NEMA 12/3R, Painted galvanized steel, Max HP:7.5, 7.5, 15, 20 hp (@208,240,480,600 V), Three-pole, Product category: enclosed rotary non-fusible, R-Series, 600 V



Photo is representative

General specifications

Product Name	Catalog Number
Eaton enclosed rotary disconnect switch	ER53030UD
UPC	Product Length/Depth
786685466040	10.4 in
Product Height	Product Width
6.7 in	7.2 in
Product Weight	Warranty
6.2 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	Catalog Notes
UL Listed CSA Certified	NEMA Type 12 enclosures (16–80A) can be field modified to meet NEMA Type 3R rainproof requirements when a factory-provided drain hole is opened.

Physical Attributes

Enclosure

NEMA 12, NEMA 3R

Enclosure material

Painted galvanized steel

Number of poles

Three-pole

Series

R-Series

Type

Enclosed rotary disconnect

Performance Ratings

Amperage Rating

30A

HP rating - max

7.5, 7.5, 15, 20 hp (@208,240,480,600 V)

Voltage rating

600 V

Miscellaneous

Product Category

Enclosed rotary non-fusible

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Multimedia

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - ER53030UD](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)