

Eaton ER53030UW

Catalog Number: ER53030UW

Eaton enclosed rotary disconnect switch, 30 A, NEMA 4X, Stainless steel, Max HP:7.5, 7.5, 15, 20 hp (@208,240,480,600 V), Three-pole, Product category: enclosed rotary non-fusible, R-Series, 600 V

General specifications



Photo is representative

Product Name

Eaton enclosed rotary disconnect switch

Catalog Number

ER53030UW

UPC

786685466101

Product Length/Depth

11 in

Product Height

7 in

Product Width

8 in

Product Weight

6.2 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed

CSA Certified

Physical Attributes

Enclosure

NEMA 4X

Enclosure material

Stainless steel

Number of poles

Three-pole

Series

R-Series

Type

Enclosed rotary disconnect

Performance Ratings

Amperage Rating

30A

HP rating - max

7.5, 7.5, 15, 20 hp (@208,240,480,600 V)

Voltage rating

600 V

Miscellaneous

Product Category

Enclosed rotary non-fusible

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Multimedia

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - ER53030UW](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia