

Eaton ER53060UW

Catalog Number: ER53060UW

Eaton enclosed rotary disconnect switch, 60 A, NEMA 4X, Stainless steel, Max HP:15, 15, 30, 30 hp (@208,240,480,600 V), Three-pole, Product category: enclosed rotary non-fusible, R-Series, 600 V



General specifications

Product Name	Catalog Number
Eaton enclosed rotary disconnect switch	ER53060UW
UPC	Product Length/Depth
786685466125	15.4 in
Product Height	Product Width
8.4 in	10 in
Product Weight	Warranty
8.4 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed
CSA Certified

Physical Attributes

Enclosure

NEMA 4X

Enclosure material

Stainless steel

Number of poles

Three-pole

Series

R-Series

Type

Enclosed rotary disconnect

Performance Ratings

Amperage Rating

60A

HP rating - max

15, 15, 30, 30 hp (@208,240,480,600 V)

Voltage rating

600 V

Miscellaneous

Product Category

Enclosed rotary non-fusible

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Multimedia

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - ER53060UW](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)