

ERT713

Black Metal Baffle




- Socket supporting trim
- ERT713 - Friction clip retention
- ERT713TS - Torsion spring retention

EI700	40W A19, 65W BR30, 75W PAR30, 75W PAR30L, 90W BR40
EI700AT	
EI700R	
EI700RAT	
EI700NB	40W A19, 65W BR30, 75W R30, 75W PAR30, 75W PAR30L, 90W BR40
EI700ATNB	

ET700	75W PAR30L, 85W BR30, 100W R30, 100W A19, 120W BR40
ET700R	65W BR30, 75W PAR30L

EI700U	60W A19, 75W PAR30, 75W PAR30L, 85W BR30, 120W BR40
EI700UAT	



ERT713TS
High Gloss Appliance White Trim
with Black Baffle and Torsion
Spring Construction

ERT713
High Gloss Appliance White Trim
with Black Baffle

ERT713WHT

White Metal Baffle




- Socket supporting trim
- ERT713WHT - Friction clip retention
- ERT713WHTTS - Torsion spring retention

EI700	40W A19, 65W BR30, 75W R30, 75W PAR30, 75W PAR30L, 90W BR40
EI700AT	
EI700R	
EI700RAT	
EI700NB	
EI700ATNB	

ET700	75W PAR30L, 85W BR30, 100W R30, 100W A19, 120W BR40
ET700R	65W BR30, 75W PAR30L

EI700U	60W A19, 75W PAR30, 75W PAR30L, 85W BR30, 100W R30, 120W BR40
EI700UAT	



ERT713WHTTS
High Gloss Appliance White Trim
with White Baffle and Torsion
Spring Construction

ERT713WHT
High Gloss Appliance White Trim
with White Baffle

ERT713L

Black Metal Baffle





- Provides deeper lamp regression
- Socket supporting trim
- ERT713L - Friction clip retention
- ERT713LTS - Torsion spring retention

EI700	75W BR40, 65W BR30, 75W PAR30L
EI700AT	
EI700R	
EI700RAT	
EI700NB	
EI700ATNB	

ET700	75W A19, 75W PAR30L, 75W PAR30, 85W BR30, 100W R30, 120W BR40, 150W R40
ET700R	65W BR30, 75W PAR30L, 150W R40

EI700U	40W A19, 75W PAR30, 75W PAR30L, 85W BR30, 120W BR40
EI700UAT	



ERT713LTS
High Gloss Appliance White Trim
with Black Baffle and Torsion
Spring Construction

ERT713L
High Gloss Appliance White Trim
with Black Baffle

ADV111764

September 22, 2011 4:22 PM

Note: Specifications and Dimensions subject to change without notice.

Visit our web site at www.cooperlighting.com

ERT713

Black Metal Baffle




- Socket supporting trim
- ERT713 - Friction clip retention
- ERT713TS - Torsion spring retention

EI700	40W A19, 65W BR30, 75W PAR30, 75W PAR30L, 90W BR40
EI700AT	
EI700R	
EI700RAT	
EI700NB	40W A19, 65W BR30, 75W R30, 75W PAR30, 75W PAR30L, 90W BR40
EI700ATNB	

ET700	75W PAR30L, 85W BR30, 100W R30, 100W A19, 120W BR40
ET700R	65W BR30, 75W PAR30L

EI700U	60W A19, 75W PAR30, 75W PAR30L, 85W BR30, 120W BR40
EI700UAT	



Height: 5" [127mm]
OD: 7-1/4" [184mm]



ERT713TS
High Gloss Appliance White Trim
with Black Baffle and Torsion
Spring Construction

ERT713
High Gloss Appliance White Trim
with Black Baffle

ERT713WHT

White Metal Baffle




- Socket supporting trim
- ERT713WHT - Friction clip retention
- ERT713WHTTS - Torsion spring retention

EI700	40W A19, 65W BR30, 75W R30, 75W PAR30, 75W PAR30L, 90W BR40
EI700AT	
EI700R	
EI700RAT	
EI700NB	
EI700ATNB	

ET700	75W PAR30L, 85W BR30, 100W R30, 100W A19, 120W BR40
ET700R	65W BR30, 75W PAR30L

EI700U	60W A19, 75W PAR30, 75W PAR30L, 85W BR30, 100W R30, 120W BR40
EI700UAT	



Height: 5-3/8" [136mm]
OD: 7-1/4" [184mm]



ERT713WHTTS
High Gloss Appliance White Trim
with White Baffle and Torsion
Spring Construction

ERT713WHT
High Gloss Appliance White Trim
with White Baffle

ERT713L

Black Metal Baffle




- Provides deeper lamp regression
- Socket supporting trim
- ERT713L - Friction clip retention
- ERT713LTS - Torsion spring retention

EI700	75W BR40, 65W BR30, 75W PAR30L
EI700AT	
EI700R	
EI700RAT	
EI700NB	
EI700ATNB	

ET700	75W A19, 75W PAR30L, 75W PAR30, 85W BR30, 100W R30, 120W BR40, 150W R40
ET700R	65W BR30, 75W PAR30L, 150W R40

EI700U	40W A19, 75W PAR30, 75W PAR30L, 85W BR30, 120W BR40
EI700UAT	



Height: 5-3/8" [136mm]
OD: 7-1/4" [184mm]



ERT713LTS
High Gloss Appliance White Trim
with Black Baffle and Torsion
Spring Construction

ERT713L
High Gloss Appliance White Trim
with Black Baffle

ADV111764

September 22, 2011 4:22 PM

Note: Specifications and Dimensions subject to change without notice.

Visit our web site at www.cooperlighting.com