



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ESGS40 #2-4/0 Awg In-Line Gel Splice Kit (W/Connector)

Nsi Industries

Catalog Number	ESGS40
Manufacturer	Nsi Industries
Description	Splice Kit, Copper/Aluminum Conductor Material, Black Insulation Color, -40 °F Operating Temperature, +194 °F Operating Temperature, 4.229 In Overall Length, 1000 V, 0.26 LB
Weight per unit	0.2600 (lbs/each)
Product Category	Splicing & Terminating Kits

Features

Cable Size	2-4/0 AWG
Cable Type	Class A-B
Voltage Rating	1000 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Black
-------	-------

Descriptions

Description	#2-4/0 AWG IN-LINE GEL SPLICE KIT (W/CONNECTOR)
extra long description	NSI ESGS-4/0 Easy-Splice Gel Tap 2/
Special Features	Provides Sealed Splice For Underground, Buried, And Overhead Applications

Manufacturer Information

GTIN	00662381168610
UPC	662381168610

Taxonomies, Classifications, and Categories

Category Description	SPLICE KITS
Type	In-Line Gel Splice Kit

Packaging

Carton	3
Weight Per each	0.26

Uses, Certifications, and Standards

Application	Splicing Wire
Operating Temperature	-40 C To 90 C
standard	ANSI C119.1-1986 Qualified