



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1811 N. University Suite 100
70507-0000, LA Lafayette
Phone: 337-235-7681
Fax: 337-235-7725



ESV10BXQ 12-10AWG 1.22" Ylw Butt Splice

Panduit Corporation

Catalog Number	ESV10BXQ
Manufacturer	Panduit Corporation
Description	Stronghold ESV10BX-Q Contractor Grade Vinyl Insulated Butt Splices Are A Reliable and Economical Option That Withstand A Wide Range Of General-Purpose Applications. They Are Designed to Splice Two Solid or Stranded Wires Together to Repair or Lengthen Wires. Accommodates 12-10 Awg, Are Yellow In Color, and Come In Packages Of 25.
Weight per unit	0.0500 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Expanded
insulation	Vinyl
Material	Copper
media	Yes
Wire Size	12 - 10 AWG

Material, Color, and Finish

Color	Yellow
Finish	Tinned

Descriptions

Description	12-10AWG 1.22" YLW BUTT SPLICE
extra long description	PAN ESV10BX-Q StrongHold™ ESV10BX-Q
Long Description	StrongHold ESV10BX-Q Contractor Grade Vinyl Insulated Butt Splices are a reliable and economical option that withstand a wide range of general-purpose applications. They are designed to splice two solid or stranded wires together to repair or lengthen wires. Accommodates 12-10 AWG, are yellow in color, and come in packages of 25.
Product Type	Stronghold™ ESV10BX-Q Butt Splice, Yellow, Vinyl, 1.22", 12-

Manufacturer Information

Brand	Panduit Corporation
GTIN	00074983279784
Manufacturers Part Number	ESV10BX-Q
UPC	074983279784

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Butt Splice



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1811 N. University Suite 100
70507-0000, LA Lafayette
Phone: 337-235-7681
Fax: 337-235-7725

Packaging

Carton	25
Package	250
Weight Per each	0.05

Uses, Certifications, and Standards

Mounting	5/16
standard	UL Listed, CSA Certified