ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
3705 Lee Street
Alexandria, LA 71302-0
Phone: 3184451336
Fax: 3184458356



ET270 DIGITAL MULTITESTER MULTIMETER W RECEPTACLE TESTER

KLEIN TOOLS

Catalog Number	ET270
Manufacturer	KLEIN TOOLS
Description	Klein Tools' ET270 is an auto-ranging digital multi-tester that measures AC/DC voltage, resistance, continuity, and performs a battery test. It also tests wiring conditions in standard 120VAC and GFCI electrical receptacles and inspects North American GFCI devices. Comes with Right-Angle Test Leads, Receptacle Test Cord, Instructions, and all required batteries.
Weight per unit	1.3 (lbs/each)
Product Category	Tools & Testers

Features

Accuracy	65°F to 83°F (18°C to 28°C): +/- (% of Reading + Number of Least Significant Digits)
Capacitance	—
Material	ABS and Electrical Components
Overall Height	1.84" (4.5 cm)
Overall Width	3.13" (7.9 cm)
Temperature Range	—
Voltage	600V AC/DC
Display	4000 Count LCD
Functions	AC/DC Voltage;Battery Test;Continuity;Detects and Identifies Common Wiring Problems in GFCI Receptacles;Finds Breaker to Corresponding Receptacle;Resistance;Shows Amount of Time it Takes to Trip GFCI
Included	Batteries;Digital Multimeter;Receptacle Test Cord;Right-Angle Test Leads;Storage Pouch;User Manual

Material, Color, and Finish

Color	Orange/ Black

Dimensions and Weight

Overall Length	6.41" (16.3 cm)

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
3705 Lee Street
Alexandria, LA 71302-0
Phone: 3184451336
Fax: 3184458356

Descriptions

Description	DIGITAL MULTITESTER MULTIMETER W RECEPTACLE TESTER
Features	Klein Tools' ET270 is an auto-ranging digital multi-tester that measures AC/DC voltage, resistance, continuity, and performs a battery test. It also tests wiring conditions in standard 120VAC and GFCI electrical receptacles and inspects North American GFCI devices. Comes with Right-Angle Test Leads, Receptacle Test Cord, Instructions, and all required batteries.
Long Description	Klein Tools' ET270 is an auto-ranging digital multi-tester that measures AC/DC voltage, resistance, continuity, and performs a battery test. It also tests wiring conditions in standard 120VAC and GFCI electrical receptacles and inspects North American GFCI devices. Comes with Right-Angle Test Leads, Receptacle Test Cord, Instructions, and all required batteries.
Product Type	Digital Multi-Tester Multimeter
Special Features	Auto-Range with Option for Manual-Range;Backlight;Data Hold;Min/Max Values
Extra Long Description	KLE ET270 Digital Multi-Tester Mult

Manufacturer Information

Brand	Klein Tools
GTIN	00092644694219
Manufacturers Part Number	ET270
UPC	783523

Taxonomies, Classifications, and Categories

Category Description	TEST EQUIPMENT, TESTERS AND MULTIMETERS
Type	Digital Multimeter and GFCI Receptacle Tester

Packaging


Carton	1
Package	6
Weight	1.32 lb (0.6 kg)
Weight Per Each	1.3 (lbs/each)

Uses, Certifications, and Standards

Application	Detects and Identifies Common Wiring Problems in GFCI Receptacles;Testing and Measuring Voltage
Standard	CAT III 600V, Class 2, Double insulation

ET270
DIGITAL MULTI-TESTER DMM WITH RECEPTACLE TESTER

Two Testers in One





USE RIGHT-ANGLE TEST LEADS:

- **Measure** AC/DC Voltage, Resistance, Continuity
- **Performs** Battery Test

CAT III 600V 600V≂ 40MΩ **2 m**

Intertek 5001748

USE RECEPTACLE CORD:

- **Detect and Identify** Common Wiring Faults
- **Inspect** GFCI Devices, Including Trip Time
- **Find** Corresponding Breaker to Receptacle

KLEIN TOOLS®



DIGITAL MULTI-TESTER DMM WITH RECEPTACLE TESTER

Klein Tools' ET270 is two testers in one. It's an auto-ranging Digital Multi-Tester that measures AC/DC voltage, resistance, continuity, and performs a battery test. It also tests wiring conditions in standard 120VAC and GFCI electrical receptacles and inspects North American GFCI devices. Common wiring problems are clearly indicated on the LCD: Wired Correctly, Open Ground, Open Neutral, Open Hot, Dual Open (Neutral and Ground), Reversed Hot/Ground, and Reversed Hot/Neutral.

INSPECT GFCI OUTLETS
Including time to trip the device



FIND CORRESPONDING BREAKERS
Audible tone stops when corresponding breaker is flipped





Select FIND Button to locate the corresponding breaker

Large Backlight Display for low-light environments

Function Buttons are clearly marked

Select GFCI Button to initiate an electrical fault while in Receptacle Test Mode

Indicator LED illuminates bright RED or GREEN

Large Function Selection Switch for Battery Test, Receptacle Test, AC/DC Voltage, Continuity, or Resistance Measurements

Receptacle Jack

Test Lead Input Jacks



Includes Digital Multimeter, Right-Angle Test Leads, Receptacle Test Cord, Batteries, User Manual, Storage Pouch



Test Lead Holders located on back for convenient storage

Mount located on back secures Magnetic Hanger (sold separately) for hands-free operation

Kickstand on back for easy viewing

Cat. No.	UPC# 0-92644+	Description	Height	Length	Width	Weight
ET270	69421-9	Digital Multi-Tester DMM with Receptacle Tester	1.84" (4.5 cm)	6.41" (16.3 cm)	3.13" (7.9 cm)	1.32 lb (0.6 kg)
69410	69410-3	Replacement Test Lead Set, Right Angle				
69445	69288-8	Rare-Earth Magnetic Hanger, no Strap				
69417	69417-2	Rare-Earth Magnetic Hanger, with Strap				

⚠ Visit www.kleintools.com for warnings and instructions.

For Professionals
SINCE 1857™

KLEIN TOOLS®

See our complete line of **Test and Measurement**
www.kleintools.com

© 2023 Klein Tools, Inc.
Lincolnshire, IL 60069
78332 Rev. 09/23 A