



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9139 Linwood Ave  
71106-0000, LA Shreveport  
Phone: 318-688-9822  
Fax: 318-688-0702



## EV1010FBQ 12-10AWG #10STD Ylw Fork TRML *Panduit Corporation*

Catalog Number	EV1010FBQ
Manufacturer	Panduit Corporation
Description	Stronghold EV10-10FB-Q Contractor Grade Vinyl Insulated Fork Terminals Are A Reliable and Economical Option That Withstand A Wide Range Of General-Purpose Applications. Accommodates 12-10 Awg Wire Gauge, Compatible With #10 Stud, Are Yellow In Color, and Come In Packages Of 25.
Weight per unit	0.0500 (lbs/each)
Product Category	Small Terminals & Connectors

### Features

connection	Funnel
insulation	Vinyl
Material	Copper
media	Yes
Wire Size	10

### Material, Color, and Finish

Color	Yellow
Finish	Tinned

### Dimensions and Weight

Size	#10
------	-----

### Descriptions

Description	12-10AWG #10STD YLW FORK TRML
extra long description	PAN EV10-10FB-Q StrongHold™ EV10-10
Long Description	StrongHold EV10-10FB-Q Contractor Grade Vinyl Insulated Fork Terminals are a reliable and economical option that withstand a wide range of general-purpose applications. Accommodates 12-10 AWG wire gauge, compatible with #10 Stud, are yellow in color, and come in packages of 25.
Product Type	Stronghold™ EV10-10FB-Q Loose Piece Forks, Yellow, Vinyl, 1/

### Manufacturer Information

Brand	Panduit Corporation
GTIN	00074983280209
Manufacturers Part Number	EV10-10FB-Q
UPC	074983280209



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9139 Linwood Ave  
71106-0000, LA Shreveport  
Phone: 318-688-9822  
Fax: 318-688-0702

## Taxonomies, Classifications, and Categories

Category Description ..... TERMINALS

Type ..... Fork Terminal

## Packaging

Carton ..... 25

Package ..... 250

Weight Per each ..... 0.05

## Uses, Certifications, and Standards

Mounting ..... 5/16

standard ..... CSA Certified LR31213;UL Listed 587H E52164