



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2260 N Burton Ave Suite 100
65803-0000, MO Springfield
Phone: 417-429-1665
Fax: 417-429-1666



EV1014RBQ 12-10AWG #1/4STD Ylw Ring TRML

Panduit Corporation

Catalog Number	EV1014RBQ
Manufacturer	Panduit Corporation
Description	Stronghold EV10-14RB-Q Contractor Grade Vinyl Insulated Ring Terminals Are A Reliable and Economical Option That Withstand A Wide Range Of General-Purpose Applications. The Ring Tongue Design Assures A Secure Connection In High Vibration Applications. Accommodates 12-10 Awg, Compatible With #1/4 Stud (M6), Are Yellow In Color, and Come In Packages Of 25.
Weight per unit	0.0500 (lbs/each)
Product Category	Small Terminals & Connectors

Features

insulation	Vinyl
Material	Copper
media	Yes
Voltage Rating	600
Wire Size	10

Material, Color, and Finish

Color	Yellow
Finish	Tinned

Dimensions and Weight

Size	1/4"
------	------

Descriptions

Description	12-10AWG #1/4STD YLW RING TRML
extra long description	PAN EV10-14RB-Q StrongHold™ EV10-14
Long Description	StrongHold EV10-14RB-Q Contractor Grade Vinyl Insulated Ring Terminals are a reliable and economical option that withstand a wide range of general-purpose applications. The ring tongue design assures a secure connection in high vibration applications. Accommodates 12-10 AWG, compatible with #1/4 Stud (M6), are yellow in color, and come in packages of 25.
Product Type	Stronghold™ EV10-14RB-Q Ring Terminal, Yellow, Vinyl, 23/100

Manufacturer Information

Brand	Panduit Corporation
GTIN	00074983281862
Manufacturers Part Number	EV10-14RB-Q
UPC	074983281862



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2260 N Burton Ave Suite 100
65803-0000, MO Springfield
Phone: 417-429-1665
Fax: 417-429-1666

Taxonomies, Classifications, and Categories

Category Description TERMINALS

Type Ring Terminal

Packaging

Carton 25

Package 250

Weight Per each 0.05

Uses, Certifications, and Standards

Mounting 5/16

standard CSA Certified LR31212;UL Listed 587H E52164