


ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685





EV108FBQ 12-10AWG #8STD Ylw Fork TRML

Panduit Corporation

Catalog Number	EV108FBQ
Manufacturer	Panduit Corporation
Description	Stronghold EV10-8FB-Q Contractor Grade Vinyl Insulated Fork
·	Terminals Are A Reliable and Economical Option That Withstand
	A Wide Range Of General-Purpose Applications. Accommodates
	12-10 Awg Wire Gauge, Compatible With #8 Stud, Are Yellow In
	Color, and Come In Packages Of 25.
Weight per unit	•
Product Category	Small Terminals & Connectors
Features	
media	Yes
Descriptions	
Description	12-10AWG #8STD YLW FORK TRML
extra long description	PAN EV10-8FB-Q StrongHold™ EV10-8FB
Long Description	StrongHold EV10-8FB-Q Contractor Grade Vinyl Insulated Fork
	Terminals are a reliable and economical option that withstand a
	wide range of general-purpose applications. Accommodates
	12-10 AWG wire gauge, compatible with #8 Stud, are yellow in
	color, and come in packages of 25.
Product Type	Stronghold™ EV10-8FB-Q Loose Piece Forks, Yellow, Vinyl, 4/2
Manufacturer Information	
Brand	Panduit Corporation
GTIN	00074983280193
Manufacturers Part Number	EV10-8FB-Q
UPC	074983280193
Taxonomies, Classifications, and (Categories
Category Description	TERMINALS
Packaging	
Carton	25
Package	250
Weight Per each	0.05