



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9651 Camp Bowie West
76116-0000, TX Fort Worth
Phone: 817-560-0585
Fax: 817-560-0723



EV146FBQ 16-14AWG #6STD Blue Fork TRML *Panduit Corporation*

Catalog Number	EV146FBQ
Manufacturer	Panduit Corporation
Description	Stronghold EV14-6FB-Q Contractor Grade Insulated Fork Terminals Are A Reliable and Economical Option That Withstand A Wide Range Of General-Purpose Applications. The Fork Design Provides For Fast and Easy Installation, Without The Need to Remove Fastener. Accommodates 16-14 Awg, Compatible With #6 Stud (M3.5), Are Blue In Color, and Come In Packages Of 25.
Weight per unit	0.0500 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Funnel
insulation	Vinyl
Material	Copper
media	Yes
Wire Size	14

Material, Color, and Finish

Color	Blue
Finish	Tinned

Dimensions and Weight

Size	#6
------	----

Descriptions

Description	16-14AWG #6STD BLUE FORK TRML
extra long description	PAN EV14-6FB-Q StrongHold™ EV14-6FB
Long Description	StrongHold EV14-6FB-Q Contractor Grade Insulated Fork Terminals are a reliable and economical option that withstand a wide range of general-purpose applications. The fork design provides for fast and easy installation, without the need to remove fastener. Accommodates 16-14 AWG, compatible with #6 Stud (M3.5), are blue in color, and come in packages of 25.
Product Type	Stronghold™ EV14-6FB-Q Loose Piece Forks, Blue, Vinyl, 1/8"

Manufacturer Information

Brand	Panduit®
GTIN	00613056366381
Manufacturers Part Number	EV14-6FB-Q
UPC	613056366381



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9651 Camp Bowie West
76116-0000, TX Fort Worth
Phone: 817-560-0585
Fax: 817-560-0723

Taxonomies, Classifications, and Categories

Category Description TERMINALS

Type Fork Terminal

Packaging

Carton 25

Package 250

Weight Per each 0.05

Uses, Certifications, and Standards

Mounting 5/16

standard CSA Certified LR31212;UL Listed 587H E52164