



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2101 S Eastern Ave
73160-0000, OK Moore
Phone: 405-759-4139
Fax: 405-237-1928



EV186FBQ 22-18AWG #6STD Red Fork TRML

Panduit Corporation

Catalog Number	EV186FBQ
Manufacturer	Panduit Corporation
Description	Stronghold EV18-6FB-Q Contractor Grade Insulated Fork Terminals Are A Reliable and Economical Option That Withstand A Wide Range Of General-Purpose Applications. The Fork Design Provides For Fast and Easy Installation, Without The Need to Remove Fastener. Accommodates 22-18 Awg, Compatible With #6 Stud (M3.5), Are Red In Color, and Come In Packages Of 25.
Weight per unit	0.0700 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Funnel
insulation	Vinyl
Material	Copper
media	Yes
Wire Size	18

Material, Color, and Finish

Color	Red
Finish	Tinned

Dimensions and Weight

Size	#6
------	----

Descriptions

Description	22-18AWG #6STD RED FORK TRML
extra long description	PAN EV18-6FB-Q StrongHold™ EV18-6FB
Long Description	StrongHold EV18-6FB-Q Contractor Grade Insulated Fork Terminals are a reliable and economical option that withstand a wide range of general-purpose applications. The fork design provides for fast and easy installation, without the need to remove fastener. Accommodates 22-18 AWG, compatible with #6 Stud (M3.5), are red in color, and come in packages of 25.
Product Type	Stronghold™ EV18-6FB-Q Loose Piece Forks, Red, Vinyl, 1/8" S

Manufacturer Information

Brand	Panduit®
GTIN	00613056366442
Manufacturers Part Number	EV18-6FB-Q
UPC	613056366442



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2101 S Eastern Ave
73160-0000, OK Moore
Phone: 405-759-4139
Fax: 405-237-1928

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Fork Terminal

Packaging

Carton	25
Package	250
Weight Per each	0.07

Uses, Certifications, and Standards

Mounting standard	0.31
	CSA Certified LR31212;UL Listed 587H E52164