

Eaton EVI301

Catalog Number: EVI301

Eaton Crouse-Hinds series EVI light fixture, Medium base, Heat and impact resistant glass globe, With cast copper-free alum guard, Incandescent, Copper-free aluminum, PS-25 max. lamp size, No mounting module, Factory sealed, 120 Vac, 300W



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series EVI light fixture	EVI301
	UPC
	782274198699
Product Length/Depth	Product Height
7.25 in	13.33 in
Product Width	Product Weight
7.25 in	10.9 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Zone 1

Class I, Zone 2

Class II, Division 1

Class III

NEMA Rating

4X

Ingress protection (IP) ratings

IP66

Product specifications

Lamp type

Incandescent

Base type

Medium

Wattage

300W

Mounting Method

No mounting module

Guard type

With cast guard

Material

Copper-free aluminum

Globe material

Heat and impact resistant glass

Guard material

Copper-free aluminum

Voltage rating

120 Vac

Lamp size - max

PS-25

Special features

Factory sealed

Resources

Catalogs

[EVI Explosionproof Incandescent Light Fixtures catalog page](#)

Certification reports

[EVI Explosionproof Incandescent Light Fixtures UL certification \(Marine\)](#)

[EVI Explosionproof Incandescent Light Fixtures Canadian certification](#)

[EVI Explosionproof Incandescent Light Fixtures UL certification](#)

Installation instructions

[IF 1452 - EVI Explosionproof Incandescent Light Fixtures](#)

Specifications and datasheets

[Eaton Specification Sheet - EVI301](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia