EZHH150QT

Versatile MH Floodlight with hinged lens frame and Hydroformed reflector. Field adjustable vertical and horizontal lamp positions. 50-150w QT MH. Lamp supplied.

Lamp Info		Ballast Info	
Туре:	ED17	Туре:	CWA-HPF QT
Watts:	150W	120V:	1.0/1.6A
Shape/Size:	N/A	208V:	.6/.9A
Base:	N/A	240V:	.5/.8A
ANSI:	N/A	277V:	.5/.7A
Hours:	10,000	Input Watts:	185W
Lamp Lumens:	12,500	Efficiency:	81%
Efficacy:	68 LPW		

Technical Specifications

UL Listing:

Suitable for wet locations. Suitable for mounting within 1.2m (4ft) of the ground.

Housing:

Precision die cast aluminum. 1/2" NPS threaded arm with locking swivel.

Reflector:

Hydroformed aluminum. Field adjustable vertical or horizontal.

Lens Gasket:

High temperature tubular silicone set in die cast retaining groove remains in place during relamping.

Lens Frame:

Precision die cast aluminum. Hinged for easy access.

Socket:

Porcelain 4kv Pulse Rated socket with nickel plated screw shell.

Finish:

Our environmentally friendly polyester powder coatings are formulated for high-durability and long-lasting color, and contains no VOC or toxic heavy metals.

Ground Mounting:

Use the new MPM19 PVC Mighty Post with aluminum cap for sturdy installation.

Quad Tap:


Fixture works with 120, 208, 240 and 277 Volts .

EPA: 0.6





Weight: 15.0 lbs



Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.