



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EZT2048S Ez Trim Surface Unvented For 20"W X 48"H Box Wem2 *Eaton Corp*

Catalog Number	EZT2048S
Manufacturer	Eaton Corp
Description	Eaton Pow-R-Xpress Ez Trim Surface, Unvented For 20"W X 48"H Box WEM2 Keyed
Weight per unit	35.0 (lbs/each)
Product Category	Fronts & Trims

### Features

dimensions	48.0000 IN X 20.0000 IN X 1.0000 IN
Material	Copper
media	Yes

### Descriptions

Description	EZ TRIM SURFACE UNVENTED FOR 20"W X 48"H BOX WEM2
extra long description	ETN EZT2048S EZ TRIM,S,UNVENT 20WX4
Features	The Pow-R-Xpress program brings to you a new set of products - Pow-R-Xpress panelboards. The Pow-R-Xpress products include interiors; type 1 and 3R boxes; surface and flush trims; main breaker kits; branch breakers; lug kits; service entrance kits; ground kits; and 200% neutral kits. In addition, the distributor stocking program can be used with various Eaton commercial distribution products and is designed to meet UL67 standards for use in data center, industrial, commercial and healthcare facilities.
Long Description	Eaton Pow-R-Xpress EZ trim surface, unvented for 20"W X 48"H box WEM2 Keyed
Product Type	Ez Trim, S, Unvent 20WX48H WEM2 Keyed
Special Features	Pow-R-Xpress

### Manufacturer Information

Brand	Eaton
GTIN	00782116934225
Manufacturers Part Number	EZT2048S
UPC	782116934225

### Taxonomies, Classifications, and Categories

Category Description	Panelboard Boxes, Covers, Latches, Directories
Type	Accessory

### Availability

Status	Inactive
--------	----------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	35

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
standard	UL 67