



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1500 West Cotton
75604-0000, TX Longview
Phone: 903-757-8491
Fax: 903-758-0441



F030841XPSSEC03 30W T8 48" 41K 85 Cri Min Start 550V

Sylvania-Ledvance

Catalog Number	F030841XPSSEC03
Manufacturer	Sylvania-Ledvance
Description	30W, 48" Mol, T8 Octron Supersaver Fluorescent Lamp, 4100K Color Temperature, Rare Earth Phosphor, 85 Cri, Suitable For Use On Rapid or Instant Ballasts or Other T8 Ballasts With Minimum Starting Voltage Of 550V, Ecologic 3
Weight per unit	0.4500 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
average life	40000
Base	Medium Bipin
bulb type	T8
Lamp Type	RAPID & INSTANT START
Shape	T8
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	30

Material, Color, and Finish

color rendering index (cri)	85
color temperature	4100
Finish	Phosphor Coated

Descriptions

Description	30W T8 48" 41K 85 CRI MIN START 550V
extra long description	SYL F030841XPSSECO3/22062 F030841XP
Long Description	30W, 48" MOL, T8 OCTRON SuperSaver fluorescent lamp, 4100K color temperature, rare earth phosphor, 85 CRI, suitable for use on rapid or instant ballasts or other T8 ballasts with minimum starting voltage of 550V, ECOLOGIC 3
Product Type	F030841XPSSECO3 30/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135220623
Manufacturers Part Number	FO30/841/XP/SS/ECO3/22062
UPC	046135220623



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1500 West Cotton
75604-0000, TX Longview
Phone: 903-757-8491
Fax: 903-758-0441

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	30
Weight Per each	0.45

Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------