


45749 - F17T8/SPX41/ECO

GE Ecolux® Starcoat® T8

• Passes TCLP, which can lower disposal costs.







CAUTIONS & WARNINGS

Caution


- · Lamp may shatter and cause injury if broken
- Wear safety glasses and gloves when handling lamp.
- Do not use excessive force when installing lamp.

Warning


- Risk of Electric Shock
- Turn power off before inspection, installation or removal.

GRAPHS & CHARTS

Graphs_Spectral Power Distribution



Graphs_Lumen Maintenance



GENERAL CHARACTERISTICS Linear Fluorescent - Straight

Linear

12.0 h Soda lime

10.0 °C

lumen hour

Full Wattage

TCLP compliant

30000.0 hrs

15000 h @ 3 h

20000 h @ 12 h

30000.0 @ 3.0/36000.0 @

77 picograms Hg per mean

Medium Bi-Pin (G13)

Τ8

Lamp Type

Bulb Base Rated Life Rated Life (instant start) @ Time Rated Life (rapid start) @ Time

Bulb Material Starting Temperature (MIN) LEED-EB MR Credit

Additional Info **Primary Application**

PHOTOMETRIC CHARACTERISTICS

Initial Lumens 1350.0 Mean Lumens 1280.0 Nominal Initial Lumens per Watt 79 **Color Temperature** 4100.0 K Color Rendering Index (CRI) 85.0 S/P Ratio (Scotopic/Photopic 1.8 Ratio)

ELECTRICAL CHARACTERISTICS

Wattage	17.0
Voltage	70.0
Open Circuit Voltage (rapid	285.0 V
start) (MAX)	
Open Circuit Voltage (rapid	210 V @ 10 °C
start) Min @ Temperature	
Cathode Resistance Ratio - Rh/	4.25
Rc (MIN)	
Cathode Resistance Ratio - Rh/	6.5
Rc (MAX)	
Current Crest Factor (MAX)	1.7

DIMENSIONS

Maximum Overall Length (MOL)	24.0000 in(609.6 mm)
Minimum Overall Length	23.6700 in(601.2 mm)
Nominal Length	24.000 in(609.6 mm)
Bulb Diameter (DIA) (MIN)	0.940 in(23.9 mm)
Bulb Diameter (DIA) (MAX)	1.100 in(27.9 mm)
Bulb Diameter (DIA)	1.000 in(25.4 mm)
Max Base Face to Base Face	23.220 in(589.8 mm)
(A)	
Face to End of Opposing Pin	23.400 in(594.4 mm)
(B) (MIN)	
Face to End of Opposing Pin	23.500 in(596.9 mm)
(B) (MAX)	
End of Base Pin to End of	23.670 in(601.2 mm)
Opposite Pin End (C)	

PRODUCT INFORMATION

Product Code	45749
Description	F17T8/SPX41/ECO
ANSI Code	1001-1
Standard Package	Case
Standard Package GTIN	10043168457498
Standard Package Quantity	24
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard	24
Package	
UPC	043168457491

Graphs_Lamp Mortality For additional information, visit www.gelighting.com

