



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2400 N Stallings Drive
75964-0000, TX Nacogdoches
Phone: 936-715-4010
Fax: 936-715-4039



F20T12CW 20W T12 24" Cool White 62 CRI Bi-Pin Fluor Lamp

Ge By Current Lamps

Catalog Number	F20T12CW
Manufacturer	Ge By Current Lamps
Description	Ge Ecolux®, 20 WTT, 1200 LM, 4100 KV, 60 CRI, 1.5 In Diameter, 24 In Length, Medium Bi-Pin (G13) Base, 9000 HR Average Life
Weight per unit	0.3600 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

average life	9000
Base	Medium Bi-Pin (G13)
lumens	1200
Wattage	20

Material, Color, and Finish

color rendering index (cri)	60.0
color temperature	4100.0

Dimensions and Weight

Diameter	1.5
Length	24

Descriptions

Description	20W T12 24" COOL WHITE 62 CRI BI-PIN FLUOR LAMP
extra long description	GEL F20T12/CW/ECO 80045 SLIM LINE /
Long Description	GE Ecolux®, 20 WTT, 1200 LM, 4100 KV, 60 CRI, 1.5 IN Diameter, 24 IN Length, Medium Bi-Pin (G13) Base, 9000 HR Average Life
Product Type	80045 Slim Line / F20

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168800457
Manufacturers Part Number	F20T12/CW/ECO
UPC	043168800457

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Package	24
Weight Per each	0.36



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2400 N Stallings Drive
75964-0000, TX Nacogdoches
Phone: 936-715-4010
Fax: 936-715-4039

Uses, Certifications, and Standards

Application

Full Wattage