


38201 - F25T12/CW/33 6PK

GE garage & basement 25 watt T12 1-pack

- Passes TCLP, which can lower disposal costs.
- 1.5 inch diameter T12 with medium bi-pin (g13) base
- 4100K cool white light appearance
- · Cool white light perfect for sizable spaces
- For use in large spaces such as basements and garages
- GE garage & basement fluorescent bulbs' cool white light is perfect for illuminating sizable spaces throughout your home. Use in large open spaces in your home including finished and unfinished basements, garages and rec rooms
- Lasts 3.4 years based on 6 hours per day usage
- 33 inches long





CAUTIONS & WARNINGS

Caution


- Lamp may shatter and cause injury if broken
- Wear safety glasses and gloves when handling lamp.
- Do not use excessive force when installing lamp.

Warning

- Risk of Electric Shock
- Turn power off before inspection, installation or removal.

GRAPHS & CHARTS

Graphs_Lamp Mortality



GENERAL CHARACTERISTICS

Lamp Type Linear Fluorescent - Straight

Linear

Bulb T12

Base Medium Bi-Pin (G13)
Rated Life 7500.0 hrs
Rated Life (instant start) @ 7500 h @ 3 h

Time

Bulb Material Soda lime Starting Temperature (MIN) 10.0 °C

LEED-EB MR Credit 4776 picograms Hg per

mean lumen hour

Additional Info TCLP compliant
Primary Application Appliance; Speciality

PHOTOMETRIC CHARACTERISTICS

Initial Lumens 1860.0
Mean Lumens 1675.0
Nominal Initial Lumens per Watt
Color Temperature 4100.0 K
Color Rendering Index (CRI) 60.0

ELECTRICAL CHARACTERISTICS

Wattage 25.0 Voltage 61.0 Cathode Resistance Ratio - Rh/ 6.5

Rc (MAX)

Preheat Voltage (MIN) 4.25 V

DIMENSIONS

Maximum Overall Length 33.0000 in(838.2 mm)

(MOL)

 Nominal Length
 33.000 in(838.2 mm)

 Bulb Diameter (DIA) (MAX)
 1.590 in(40.4 mm)

 Bulb Diameter (DIA)
 1.500 in(38.1 mm)

PRODUCT INFORMATION

No Of Items Per Standard

Product Code 38201

Description F25T12/CW/33 6PK

24

Standard Package BUNDLE

Standard Package GTIN 00043168382014

Standard Package Quantity 24
Sales Unit Unit
No Of Items Per Sales Unit 1

Package

UPC 043168980760