



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F25T8SP35ECO 25W T8 36" 3500K 78 Cri Bi-Pin Energy Saving

Ge By Current Lamps

Catalog Number	F25T8SP35ECO
Manufacturer	Ge By Current Lamps
Description	Ge Ecolux®, 25 WTT, 2080 LM, 3500 KV, 78 Cri, 1 In Diameter, 35.78 In Length, Medium Bi-Pin (G13) Base, 30000 HR Average Life
Weight per unit	0.3500 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

average life	30000
Base	Medium Bi-Pin (G13)
lumens	2080
Wattage	25

Material, Color, and Finish

color rendering index (cri)	78.0
color temperature	3500.0

Dimensions and Weight

Diameter	1
Length	35.78

Descriptions

Description	25W T8 36" 3500K 78 CRI BI-PIN ENERGY SAVING
extra long description	GEL F25T8/SP35/ECO 45754 FLUORESCEN
Long Description	GE Ecolux®, 25 WTT, 2080 LM, 3500 KV, 78 CRI, 1 IN Diameter, 35.78 IN Length, Medium Bi-Pin (G13) Base, 30000 HR Average Life
Product Type	45754 Fluorescent

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168457545
Manufacturers Part Number	F25T8/SP35/ECO
UPC	043168457545

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Packaging

Carton	1
Package	24
Weight Per each	0.35



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Full Wattage