GE Lighting

66471 - F28T8/XL/SPP35/ECO

F28T8/XLSPP35ECO-T8-SPP NEW TECHNICAL LAMPS

• Meets TCLP requirements



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight Linear
Bulb	T8
Base	Medium Bi-Pin (G13)
Rated Life (NOM)	40000.0 h
Rated Life (instant start) @ Time	20000 h @ 3 h 28000 h @ 12 h
Rated Life (rapid start) @ Time	40000.0 @ 3.0/45000.0 @ 12.0 h
Bulb Material	Sodalime glass
Starting Temperature (MIN)	15.0 °C
Mercury Content (NOM)	2.95 mg
Picograms of Mercury (NOM)	30.22541 pg
Primary Application	Energy Saving

PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	2600.0
Mean Lumens (NOM)	2440.0
Nominal Initial Lumens per Watt (NOM)	92.85714
Color Temperature (NOM)	3500.0 K
Color Rendering Index (CRI) (NOM)	80.0

ELECTRICAL CHARACTERISTICS

Wattage (NOM)	28.0

DIMENSIONS

Maximum Overall Length (MOL) (NOM)	48.000 in(1219.2 mm)
Nominal Length (NOM)	48.000 in(1219.2 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)

PRODUCT INFORMATION

Product Code	66471
Description	F28T8/XL/SPP35/ECO
Standard Package	Case
Standard Package GTIN	10043168664711
Standard Package Quantity	36
Sales Unit	Unit
No Of Items Per Sales Unit	1
UPC	043168664714

GE Lighting

66471 - F28T8/XL/SPP35/ECO

F28T8/XLSPP35ECO-T8-SPP NEW TECHNICAL LAMPS

• Meets TCLP requirements



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight Linear
Bulb	T8
Base	Medium Bi-Pin (G13)
Rated Life (NOM)	40000.0 h
Rated Life (instant start) @ Time	20000 h @ 3 h 28000 h @ 12 h
Rated Life (rapid start) @ Time	40000.0 @ 3.0/45000.0 @ 12.0 h
Bulb Material	Sodalime glass
Starting Temperature (MIN)	15.0 °C
Mercury Content (NOM)	2.95 mg
Picograms of Mercury (NOM)	30.22541 pg
Primary Application	Energy Saving

PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	2600.0
Mean Lumens (NOM)	2440.0
Nominal Initial Lumens per Watt (NOM)	92.85714
Color Temperature (NOM)	3500.0 K
Color Rendering Index (CRI) (NOM)	80.0

ELECTRICAL CHARACTERISTICS

Wattage (NOM)	28.0

DIMENSIONS

Maximum Overall Length (MOL) (NOM)	48.000 in(1219.2 mm)
Nominal Length (NOM)	48.000 in(1219.2 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)

PRODUCT INFORMATION

Product Code	66471
Description	F28T8/XL/SPP35/ECO
Standard Package	Case
Standard Package GTIN	10043168664711
Standard Package Quantity	36
Sales Unit	Unit
No Of Items Per Sales Unit	1
UPC	043168664714