



Med Bi Pin




T8 Med Bi Pin




T-8 Single Pin Slimline


Nom. Watts	Nom. Length (in.)	Base	Bulb	Order Code	Description	Pkg. Qty.	Rated Life (hours)	Initial Lumens	Design Lumens	Kelvin Temp.	CRI
T-8 HIGH PERFORMANCE											
28	48	Med Bi Pin	T8	01900	F28T8/830/ES Terra-Lux Energy Saver	25	24000	2775	2635	3000	85
				01901	F28T8/835/ES Terra-Lux Energy Saver	25	24000	2775	2635	3500	85
				01902	F28T8/841/ES Terra-Lux Energy Saver	25	24000	2775	2635	4100	85
				01903	F28T8/850/ES Terra-Lux Energy Saver	25	24000	2775	2635	5000	85
32	48	Med Bi Pin	T8	01920	F32T8/835/HL Terra-Lux High Lumen	25	24000	3100	2915	3500	85
				01921	F32T8/841/HL Terra-Lux High Lumen	25	24000	3100	2915	4100	85
				01923	F32T8/850/HL Terra-Lux High Lumen	25	24000	3100	2915	5000	85
				01711	F32T8/730 Terra-Lux	25	20000	2850	2710	3000	75
				01712	F32T8/735 Terra-Lux	25	20000	2850	2710	3500	75
				01713	F32T8/741 Terra-Lux	25	20000	2850	2710	4100	75
				01911	F32T8/741 Terra-Lux	6	20000	2850	2710	4100	75
				01705	F32T8/750 Terra-Lux	25	20000	2850	2710	5000	75
				01708	F32T8/830 Terra-Lux	25	24000	3050	2895	3000	85
				01709	F32T8/835 Terra-Lux	25	24000	3050	2895	3500	85
				01707	F32T8/841 Terra-Lux	25	24000	3050	2895	4100	85
				01704	F32T8/850 Terra-Lux	25	24000	3050	2895	5000	85
				01737	F32T8/865 Terra-Lux	25	24000	3050	2895	6500	85
58	60	Med Bi Pin	T8	01740	F58T8/835	25	15000	5200	4840	3500	85
				01741	F58T8/841	25	15000	5200	4840	4100	85
70	72	Med Bi Pin	T8	01751	F70T8/841	25	15000	6000	5580	4100	85
				51752	F70T8/860	25	15000	6000	5580	6000	85
96	96	Single Pin	T8	60453	F96T8/730	24	15000	5700	5190	3000	75
				60439	F96T8/735	24	15000	5700	5190	3500	75
				60438	F96T8/741	24	15000	5700	5190	4100	75
T-8 STANDARD											
14	15	Med Bi Pin	T8	60410	F14T8/CW Cool White	25	9000	710	590	4100	62
15	18	Med Bi Pin	T8	19001	F15T8/CW Cool White	6	10000	870	765	4100	62
				01714	F15T8/CW Cool White	25	10000	870	765	4100	62
				01715	F15T8/D Daylight	25	10000	870	765	6500	76
				60416	F15T8/D Daylight	112	10000	870	765	6500	76
30	36	Med Bi Pin	T8	17923	F30T8/CW Cool White	6	7500	2200	2000	4100	62
				60412	F30T8/CW Cool White	30	7500	2200	2000	4100	62
				60414	F30T8/D Daylight	25	7500	820	655	6500	76
32	48	Med Bi Pin	T8	17944	F32T8/EXCELLA	30	20000	2650	2895	5765	91
T10											
40	48	Med Bi Pin	T10	30539	F40T10/4100	25	24000	3700	3300	4100	88
				30540	F40T10/5000	25	24000	3700	3300	5000	88
T-12 ENERGY SAVER											
34	48	Med Bi Pin	T12	30530	F34T12/CW/ES Terra-Lux	30	20000	2650	2300	4100	62
				30532	F34T12/CW/ES/Overwrap Terra-Lux	30	20000	2650	2300	4100	62
				30534	F34T12/CW/ES/Strong Box Terra-Lux	6	20000	2650	2300	4100	62
				30531	F34T12/CW/ES/Strong Box Terra-Lux	30	20000	2650	2300	4100	62
				30537	F34T12/WW/ES Terra-Lux	30	20000	2700	2350	3000	53
				30576	F34T12/WW/ES/Overwrap Terra-Lux	30	20000	2700	2350	3000	53
				30535	F34T12/WW/ES/Strong Box Terra-Lux	6	20000	2700	2350	3000	53
				30538	F34T12/WW/ES/Strong Box Terra-Lux	30	20000	2700	2350	3000	53
				18120	F40T12/LIGHT-WHITE/ES Light White	6	20000	2850	2500	4100	62



Med Bi Pin



T8 Med Bi Pin



T-8 Single Pin Slimline

Nom. Watts	Nom. Length (in.)	Base	Bulb	Order Code	Description	Pkg. Qty.	Rated Life (hours)	Initial Lumens	Design Lumens	Kelvin Temp.	CRI
------------	-------------------	------	------	------------	-------------	-----------	--------------------	----------------	---------------	--------------	-----

T-8 HIGH PERFORMANCE

28	48	Med Bi Pin	T8	01900	F28T8/830/ES	Terra-Lux Energy Saver	25	24000	2775	2635	3000	85
				01901	F28T8/835/ES	Terra-Lux Energy Saver	25	24000	2775	2635	3500	85
				01902	F28T8/841/ES	Terra-Lux Energy Saver	25	24000	2775	2635	4100	85
				01903	F28T8/850/ES	Terra-Lux Energy Saver	25	24000	2775	2635	5000	85
32	48	Med Bi Pin	T8	01920	F32T8/835/HL	Terra-Lux High Lumen	25	24000	3100	2915	3500	85
				01921	F32T8/841/HL	Terra-Lux High Lumen	25	24000	3100	2915	4100	85
				01923	F32T8/850/HL	Terra-Lux High Lumen	25	24000	3100	2915	5000	85
				01711	F32T8/730	Terra-Lux	25	20000	2850	2710	3000	75
				01712	F32T8/735	Terra-Lux	25	20000	2850	2710	3500	75
				01713	F32T8/741	Terra-Lux	25	20000	2850	2710	4100	75
				01911	F32T8/741	Terra-Lux	6	20000	2850	2710	4100	75
				01705	F32T8/750	Terra-Lux	25	20000	2850	2710	5000	75
				01708	F32T8/830	Terra-Lux	25	24000	3050	2895	3000	85
				01709	F32T8/835	Terra-Lux	25	24000	3050	2895	3500	85
				01707	F32T8/841	Terra-Lux	25	24000	3050	2895	4100	85
				01704	F32T8/850	Terra-Lux	25	24000	3050	2895	5000	85
				01737	F32T8/865	Terra-Lux	25	24000	3050	2895	6500	85
58	60	Med Bi Pin	T8	01740	F58T8/835		25	15000	5200	4840	3500	85
				01741	F58T8/841		25	15000	5200	4840	4100	85
70	72	Med Bi Pin	T8	01751	F70T8/841		25	15000	6000	5580	4100	85
				51752	F70T8/860		25	15000	6000	5580	6000	85
96	96	Single Pin	T8	60453	F96T8/730		24	15000	5700	5190	3000	75
				60439	F96T8/735		24	15000	5700	5190	3500	75
				60438	F96T8/741		24	15000	5700	5190	4100	75

T-8 STANDARD

14	15	Med Bi Pin	T8	60410	F14T8/CW	Cool White	25	9000	710	590	4100	62
15	18	Med Bi Pin	T8	19001	F15T8/CW	Cool White	6	10000	870	765	4100	62
				01714	F15T8/CW	Cool White	25	10000	870	765	4100	62
				01715	F15T8/D	Daylight	25	10000	870	765	6500	76
				60416	F15T8/D	Daylight	112	10000	870	765	6500	76
30	36	Med Bi Pin	T8	17923	F30T8/CW	Cool White	6	7500	2200	2000	4100	62
				60412	F30T8/CW	Cool White	30	7500	2200	2000	4100	62
				60414	F30T8/D	Daylight	25	7500	820	655	6500	76
32	48	Med Bi Pin	T8	17944	F32T8/EXCELLA		30	20000	2650	2895	5765	91

T10

40	48	Med Bi Pin	T10	30539	F40T10/4100		25	24000	3700	3300	4100	88
				30540	F40T10/5000		25	24000	3700	3300	5000	88

T-12 ENERGY SAVER

34	48	Med Bi Pin	T12	30530	F34T12/CW/ES	Terra-Lux	30	20000	2650	2300	4100	62
				30532	F34T12/CW/ES/Overwrap	Terra-Lux	30	20000	2650	2300	4100	62
				30534	F34T12/CW/ES/Strong Box	Terra-Lux	6	20000	2650	2300	4100	62
				30531	F34T12/CW/ES/Strong Box	Terra-Lux	30	20000	2650	2300	4100	62
				30537	F34T12/WW/ES	Terra-Lux	30	20000	2700	2350	3000	53
				30576	F34T12/WW/ES/Overwrap	Terra-Lux	30	20000	2700	2350	3000	53
				30535	F34T12/WW/ES/Strong Box	Terra-Lux	6	20000	2700	2350	3000	53
				30538	F34T12/WW/ES/Strong Box	Terra-Lux	30	20000	2700	2350	3000	53
				18120	F40T12/LIGHT-WHITE/ES	Light White	6	20000	2850	2500	4100	62