



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4406 Highway 28 East
71360-0000, LA Pineville
Phone: 318-767-0900
Fax: 318-767-0010



F32T8SP35U6ECO 32W T8 3500K U-Bent 6" Eco

Ge By Current Lamps

Catalog Number	F32T8SP35U6ECO
Manufacturer	Ge By Current Lamps
Description	Ge Ecolux®, 32 WTT, 2700 LM, 3500 KV, 78 Cri, 1 In Diameter, 22.5 In Length, Medium Bi-Pin (G13) Base, 20000 HR Average Life
Weight per unit	0.5700 (lbs/each)
Product Category	Shape Lamps

Features

average life	20000
Base	Medium Bi-Pin (G13)
lumens	2700
Wattage	32

Material, Color, and Finish

color rendering index (cri)	78.0
color temperature	3500.0

Dimensions and Weight

Diameter	1
Length	22.5

Descriptions

Description	32W T8 3500K U-BENT 6" ECO
extra long description	GEL F32T8SP35/U6/ECO 28149 FLUORESC
Long Description	GE Ecolux®, 32 WTT, 2700 LM, 3500 KV, 78 CRI, 1 IN Diameter, 22.5 IN Length, Medium Bi-Pin (G13) Base, 20000 HR Average Life
Product Type	28149 Fluorescent

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168281492
Manufacturers Part Number	F32T8SP35/U6/ECO
UPC	043168281492

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Packaging

Carton	1
Package	12
Weight Per each	0.57

Uses, Certifications, and Standards

Application	Full Wattage
-------------	--------------