



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F32T8SP41U6ECO 28152 U-Bent Flour Lamp

Ge By Current Lamps

Catalog Number	F32T8SP41U6ECO
Manufacturer	Ge By Current Lamps
Description	Ge Ecolux®, 32 WTT, 2700 LM, 4100 KV, 78 Cri, 1 In Diameter, 22.5 In Length, Medium Bi-Pin (G13) Base, 20000 HR Average Life
Weight per unit	0.7440 (lbs/each)
Product Category	Shape Lamps

Features

average life	20000
Base	Medium Bi-Pin (G13)
lumens	2700
Wattage	32

Material, Color, and Finish

color rendering index (cri)	78.0
color temperature	4100.0

Dimensions and Weight

Diameter	1
Length	22.5

Descriptions

Description	28152 U-BENT FLOUR LAMP
extra long description	GEL F32T8SP41/U6/ECO 28152 FLUORESC
Long Description	GE Ecolux®, 32 WTT, 2700 LM, 4100 KV, 78 CRI, 1 IN Diameter, 22.5 IN Length, Medium Bi-Pin (G13) Base, 20000 HR Average Life
Product Type	28152 Fluorescent

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168281522
Manufacturers Part Number	F32T8SP41/U6/ECO
UPC	043168281522

Packaging

Carton	1
Package	12
Weight Per each	0.744

Uses, Certifications, and Standards

Application	Full Wattage
-------------	--------------