




GE
Lighting

68920 - F32T8/SPX30/U6/2

F32T8/SPX30/U6/2



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - U-Shaped
Bulb	T8
Base	Medium Bi-Pin (G13)
Rated Life (NOM)	20000.0 h
Bulb Material	Sodalime glass
Starting Temperature (MIN)	10.0 °C
Mercury Content (NOM)	90.0 mg
Picograms of Mercury (NOM)	1711.027 pg
Primary Application	Full Wattage

PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	2800.0
Mean Lumens (NOM)	2630.0
Nominal Initial Lumens per Watt (NOM)	87.5
Color Temperature (NOM)	3000.0 K
Color Rendering Index (CRI) (NOM)	82.0

ELECTRICAL CHARACTERISTICS

Wattage (NOM)	32.0
---------------	------

DIMENSIONS

Maximum Overall Length (MOL) (NOM)	22.500 in(571.5 mm)
Nominal Length (NOM)	22.500 in(571.5 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)

PRODUCT INFORMATION


Product Code	68920
Description	F32T8/SPX30/U6/2
Standard Package	Case
Standard Package GTIN	10043168689202
Standard Package Quantity	12
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	12
UPC	043168689205



GE
Lighting

68920 - F32T8/SPX30/U6/2

F32T8/SPX30/U6/2



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - U-Shaped
Bulb	T8
Base	Medium Bi-Pin (G13)
Rated Life (NOM)	20000.0 h
Bulb Material	Sodalime glass
Starting Temperature (MIN)	10.0 °C
Mercury Content (NOM)	90.0 mg
Picograms of Mercury (NOM)	1711.027 pg
Primary Application	Full Wattage

PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	2800.0
Mean Lumens (NOM)	2630.0
Nominal Initial Lumens per Watt (NOM)	87.5
Color Temperature (NOM)	3000.0 K
Color Rendering Index (CRI) (NOM)	82.0

ELECTRICAL CHARACTERISTICS

Wattage (NOM)	32.0
---------------	------

DIMENSIONS

Maximum Overall Length (MOL) (NOM)	22.500 in(571.5 mm)
Nominal Length (NOM)	22.500 in(571.5 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)

PRODUCT INFORMATION

Product Code	68920
Description	F32T8/SPX30/U6/2
Standard Package	Case
Standard Package GTIN	10043168689202
Standard Package Quantity	12
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	12
UPC	043168689205