



GE  
Lighting

**68852 - F32T8/SPX41/ECO2**  
F32T8/SPX41/ECO2



### GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight
	Linear
Bulb	T8
Base	Medium Bi-Pin (G13)
Rated Life (NOM)	30000.0 h
Rated Life (instant start) @ Time	21000 h @ 3 h
	30000 h @ 12 h
Rated Life (rapid start) @ Time	30000.0 @ 3.0/36000.0 @ 12.0 h
Bulb Material	Sodalime glass
Starting Temperature (MIN)	10.0 °C
Mercury Content (NOM)	2.95 mg
Picograms of Mercury (NOM)	35.4994 pg
Primary Application	Full Wattage

### PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	2925.0
Mean Lumens (NOM)	2770.0
Nominal Initial Lumens per Watt (NOM)	91.40625
Color Temperature (NOM)	4100.0 K
Color Rendering Index (CRI) (NOM)	85.0

### ELECTRICAL CHARACTERISTICS

Wattage (NOM)	32.0
---------------	------

### DIMENSIONS

Maximum Overall Length (MOL) (NOM)	48.000 in(1219.2 mm)
Nominal Length (NOM)	48.000 in(1219.2 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)


### PRODUCT INFORMATION

Product Code	68852
Description	F32T8/SPX41/ECO2
Standard Package	Case
Standard Package GTIN	10043168688526
Standard Package Quantity	36
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	36
UPC	043168688529



GE  
Lighting

**68852 - F32T8/SPX41/ECO2**  
F32T8/SPX41/ECO2



### GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight
Bulb	Linear
Base	T8
Rated Life (NOM)	Medium Bi-Pin (G13)
Rated Life (instant start) @ Time	30000.0 h
Rated Life (rapid start) @ Time	21000 h @ 3 h
	30000 h @ 12 h
	30000.0 @ 3.0/36000.0 @ 12.0 h
Bulb Material	Sodalime glass
Starting Temperature (MIN)	10.0 °C
Mercury Content (NOM)	2.95 mg
Picograms of Mercury (NOM)	35.4994 pg
Primary Application	Full Wattage

### PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	2925.0
Mean Lumens (NOM)	2770.0
Nominal Initial Lumens per Watt (NOM)	91.40625
Color Temperature (NOM)	4100.0 K
Color Rendering Index (CRI) (NOM)	85.0

### ELECTRICAL CHARACTERISTICS

Wattage (NOM)	32.0
---------------	------

### DIMENSIONS

Maximum Overall Length (MOL) (NOM)	48.000 in(1219.2 mm)
Nominal Length (NOM)	48.000 in(1219.2 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)

### PRODUCT INFORMATION

Product Code	68852
Description	F32T8/SPX41/ECO2
Standard Package	Case
Standard Package GTIN	10043168688526
Standard Package Quantity	36
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	36
UPC	043168688529