



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1336 Swisco Road
70665-0000, LA Sulphur
Phone: 337-533-8019
Fax: 337-533-8055



F32T8SPX41ECOCVG 32W T8 Coated 48" 4100K Med Bi-Pin Fluor Lamp

Ge By Current Lamps

Catalog Number	F32T8SPX41ECOCVG
Manufacturer	Ge By Current Lamps
Description	Ge Covrguard®, 32 WTT, 2860 LM, 4100 KV, 85 Cri, 1 In Diameter, 47.78 In Length, Medium Bi-Pin (G13) Base, 30000 HR Average Life
Weight per unit	0.4400 (lbs/each)
Product Category	Shatter Resistant Fluorescent

Features

average life	30000
Base	Medium Bi-Pin (G13)
lumens	2860
Wattage	32

Material, Color, and Finish

color rendering index (cri)	85.0
color temperature	4100.0

Dimensions and Weight

Diameter	1
Length	47.78

Descriptions

Description	32W T8 COATED 48" 4100K MED BI-PIN FLUOR LAMP
extra long description	GEL F32T8SPX41ECOCVG 41127 SLIM LIN
Long Description	GE covRguard®, 32 WTT, 2860 LM, 4100 KV, 85 CRI, 1 IN Diameter, 47.78 IN Length, Medium Bi-Pin (G13) Base, 30000 HR Average Life
Product Type	41127 Slim Line / F20

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168411271
Manufacturers Part Number	F32T8SPX41ECOCVG
UPC	043168411271

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Packaging

Carton	1
Package	36
Weight Per each	0.44



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1336 Swisco Road
70665-0000, LA Sulphur
Phone: 337-533-8019
Fax: 337-533-8055

Uses, Certifications, and Standards

Application

Shatter-Resistant