




GE
Lighting

66854 - F35/CX41/U3/WM

F35/CX41/U3/WM-CIRCLEVILLE C AND I SKUS IN PULP T



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - U-Shaped
Bulb	T12
Base	Medium Bi-Pin (G13)
Rated Life (NOM)	14000.0 h
Bulb Material	Sodalime glass
Starting Temperature (MIN)	15.0 °C
Mercury Content (NOM)	30.0 mg
Picograms of Mercury (NOM)	980.7126 pg
Primary Application	Energy Saving

PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	2300.0
Mean Lumens (NOM)	2185.0
Nominal Initial Lumens per Watt (NOM)	74.28571
Color Temperature (NOM)	4100.0 K
Color Rendering Index (CRI) (NOM)	87.0

ELECTRICAL CHARACTERISTICS

Wattage (NOM)	35.0
---------------	------

DIMENSIONS

Maximum Overall Length (MOL) (NOM)	23.000 in(584.2 mm)
Nominal Length (NOM)	23.000 in(584.2 mm)
Bulb Diameter (DIA) (NOM)	1.500 in(38.1 mm)

PRODUCT INFORMATION

Product Code	66854
Description	F35/CX41/U3/WM
Standard Package	Case
Standard Package GTIN	10043168668542
Standard Package Quantity	12
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	12
UPC	043168668545