

Bulb Shape	Base	Watts	Nominal Length (in)	Order Code	Description	Case Qty	Rated Life (hrs)	Initial Lumens	Mean Lumens	Color Temp K	CRI	High Color Rendering	Energy Savings	Reduced Wattage	Meets Federal Minimum Efficiency Standards	Footnotes	Warning and Caution Notices	Additional Information
------------	------	-------	---------------------	------------	-------------	----------	------------------	----------------	-------------	--------------	-----	----------------------	----------------	-----------------	--	-----------	-----------------------------	------------------------

T12 Lamps (continued)**4' T12 Rapid Start (continued)****25W Ecolux® Utility Shoplight**

T12	Medium Bi-Pin (G13)	25	48.0	14450	F4825W/UTECOSLV	30	12000	1860	1675	4100	60					10	101	
		25	48.0	14456	F4825W/UTECOTWN	9	12000	1860	1675	4100	60					10	101	
		25	48.0	14445	F4825W/UTECOUPC	30	12000	1860	1675	4100	60					10	101	

T12 Mod-U-Line®**T12 3-5/8" Spacing**

T12	Medium Bi-Pin (G13)	40	22.5	15259	F40SP30/U/3	12	14000	2925	2660	3000	70	☺			☺		102	
		40	22.5	14228	F40SP35/U/3	12	14000	2925	2660	3500	73	☺			☺		102	
		40	22.5	15260	F40SP41/U/3	12	14000	2925	2660	4100	72	☺			☺		102	
		40	22.5	14814	F40SPX30/U/3	12	14000	3000	2730	3000	82	☺			☺		102	
		40	22.5	14813	F40SPX35/U/3	12	14000	3000	2730	3500	82	☺			☺		102	
		40	22.5	14649	F40SCW/U/3	12	14000	2725	2400	4100	75	☺			☺		102	Super Cool White

T12 6" Spacing

T12	Medium Bi-Pin (G13)	40	22.5	15263	F40SP30/U/6	12	14000	3050	2780	3000	70	☺			☺		102	
		40	22.5	14227	F40SP35/U/6	12	14000	3050	2780	3500	73	☺			☺		102	
		40	22.5	22050	F40SP35/U/6/UPC	12	14000	3050	2780	3500	73	☺			☺		102	
		40	22.5	15265	F40SP41/U/6	12	14000	3050	2780	4100	72	☺			☺		102	
		40	22.5	14816	F40SPX30/U/6	12	14000	3100	2820	3000	82	☺			☺		102	
		40	22.5	14648	F40SCW/U/6	12	14000	2800	2460	4100	75	☺			☺		102	Super Cool White
		40	22.5	25374	F40SCW/U/6/UPC/6P	6	14000	2800	2460	4100	75	☺			☺		102	Super Cool White
		40	22.5	14815	F40SPX35/U/6	12	14000	3100	2820	3500	82	☺			☺		102	
		40	22.5	14632	F40SWW/U/6	12	14000	2800	2460	3000	75	☺			☺		102	Super Warm White

Watt-Miser® Energy Saving Lamps**T12 3-5/8" Spacing Watt-Miser®**

T12	Medium Bi-Pin (G13)	35	22.5	12199	F35CW/U/3/WM	12	14000	2200	2050	4100	60		\$	★	☺	1	102	
		35	22.5	12200	F35WW/U/3/WM	12	14000	2300	2100	3000	52		\$	★	☺	1	102	Warm White

T12 6" Spacing Watt-Miser®

T12	Medium Bi-Pin (G13)	35	22.5	12203	F35CW/U/6/WM	12	14000	2300	2100	4100	60		\$	★	☺	1	102	
		35	22.5	14471	F35CW/U/6/WM/UPC	12	14000	2300	2100	4100	60		\$	★	☺	1	102	
		35	22.5	23383	F35CW/U/6/WM/C	6	14000	2300	2100	4100	60		\$	★	☺	1	102	
		35	22.5	12207	F35WW/U/6/WM	12	14000	2350	2150	3000	52		\$	★	☺	1	102	Warm White

T12 6" Spacing Watt-Miser® Ecolux®

T12	Medium Bi-Pin (G13)	35	22.5	15622	F35CW/U/6/WM/ECO	12	18000	2600	2235	4100	62		\$	★	☺	1	102	
-----	---------------------	----	------	-------	------------------	----	-------	------	------	------	----	--	----	---	---	---	-----	--

T12 Instant Start

T12	Single Pin (Fa8)	20	24.0	10691	F24T12/CW	24	7500	1050	900	4100	60						101	
		30	36.0 cm	10709	F36T12/CW	24	7500	2000	1800	4100	60						101	
		35	42.0	10735	F42T12/CW	24	7500	2400	2210	4100	60						101	
		40	48.0	15262	F48T12/SP35	24	9000	3000	2820	3500	73	☺					101	
		40	48.0	15088	F48T12/SPX30	24	9000	3050	2870	3000	82	☺					101	
		40	48.0	15116	F48T12/SPX35	24	9000	3050	2870	3500	82	☺					101	
		40	48.0	10748	F48T12/CW	24	9000	2875	2650	4100	60						101	
		40	48.0	20461	F48T12CW/UPC 6PK	24	9000	2875	2650	4100	60						101	

Watt-Miser® Energy Saving Lamps

T12	Single Pin (Fa8)	30	48.0	14319	F48T12/SP35/WM	24	9000	2575	2420	3500	73	☺	\$	★		1	101	
		30	48.0	13048	F48T12/SP41/WM	24	9000	2575	2420	4100	72	☺	\$	★		1	101	
		30	48.0	44967	F48T12/CW/WM	24	9000	2475	2400	4100	60		\$	★		1	101	

8' T12 Instant Start**8' Instant Start Standard**

T12	Single Pin (Fa8)	75	96.0	15357	F96T12SP30 15PK	15	12000	6500	6110	3000	70	☺			☺		101	
		75	96.0	14067	F96T12SP35 15PK	15	12000	6500	6110	3500	73	☺			☺		101	
		75	96.0	15358	F96T12/SP41 15PK	15	12000	6500	6110	4100	72	☺			☺		101	
		75	96.0	12127	F96T12/SP65	15	12000	6125	5760	6500	75	☺			☺		101	
		75	96.0	15110	F96T12SPX30 15PK	15	12000	6800	6390	3000	82	☺			☺		101	
		75	96.0	15101	F96T12SPX35 15PK	15	12000	6800	6390	3500	82	☺			☺		101	
		75	96.0	15335	F96T12SPX41 15PK	15	12000	6800	6390	4100	80	☺			☺		101	
		75	96.0	23466	F96T12/SPX50	15	12000	6250	5880	5000	80	☺			☺		101	
		75	96.0	14652	F96T12/DX	15	12000	4500	4050	6500	84	☺			☺		101	Daylight Deluxe

Bulb Shape	Base	Watts	Nominal Length (in)	Order Code	Description	Case Qty	Rated Life (hrs)	Initial Lumens	Mean Lumens	Color Temp K	CRI	High Color Rendering	Energy Savings	Reduced Wattage	Meets Federal Minimum Efficiency Standards	Footnotes	Warning and Caution Notices	Additional Information			
T12 Lamps (continued)																					
4' T12 Rapid Start (continued)																					
25W Ecolux® Utility Shoplight																					
T12	Medium Bi-Pin (G13)	25	48.0	14450	F4825W/UTECOSLV	30	12000	1860	1675	4100	60					10	101				
		25	48.0	14456	F4825W/UTECOTWN	9	12000	1860	1675	4100	60					10	101				
		25	48.0	14445	F4825W/UTECOUPC	30	12000	1860	1675	4100	60					10	101				
T12 Mod-U-Line®																					
T12 3-5/8" Spacing																					
T12	Medium Bi-Pin (G13)	40	22.5	15259	F40SP30/U/3	12	14000	2925	2660	3000	70					Ⓔ		102			
		40	22.5	14228	F40SP35/U/3	12	14000	2925	2660	3500	73					Ⓔ		102			
		40	22.5	15260	F40SP41/U/3	12	14000	2925	2660	4100	72					Ⓔ		102			
		40	22.5	14814	F40SPX30/U/3	12	14000	3000	2730	3000	82					Ⓔ		102			
		40	22.5	14813	F40SPX35/U/3	12	14000	3000	2730	3500	82					Ⓔ		102			
		40	22.5	14649	F40SCW/U/3	12	14000	2725	2400	4100	75					Ⓔ		102	Super Cool White		
T12 6" Spacing																					
T12	Medium Bi-Pin (G13)	40	22.5	15263	F40SP30/U/6	12	14000	3050	2780	3000	70					Ⓔ		102			
		40	22.5	14227	F40SP35/U/6	12	14000	3050	2780	3500	73					Ⓔ		102			
		40	22.5	22050	F40SP35/U/6/UPC	12	14000	3050	2780	3500	73					Ⓔ		102			
		40	22.5	15265	F40SP41/U/6	12	14000	3050	2780	4100	72					Ⓔ		102			
		40	22.5	14816	F40SPX30/U/6	12	14000	3100	2820	3000	82					Ⓔ		102			
		40	22.5	14648	F40SCW/U/6	12	14000	2800	2460	4100	75					Ⓔ		102	Super Cool White		
		40	22.5	25374	F40SCW/U/6/UPC/6P	6	14000	2800	2460	4100	75					Ⓔ		102	Super Cool White		
		40	22.5	14815	F40SPX35/U/6	12	14000	3100	2820	3500	82					Ⓔ		102			
40	22.5	14632	F40SWW/U/6	12	14000	2800	2460	3000	75					Ⓔ		102	Super Warm White				
Watt-Miser® Energy Saving Lamps																					
T12 3-5/8" Spacing Watt-Miser®																					
T12	Medium Bi-Pin (G13)	35	22.5	12199	F35CW/U/3/WM	12	14000	2200	2050	4100	60		\$		Ⓔ	1	102				
		35	22.5	12200	F35WW/U/3/WM	12	14000	2300	2100	3000	52		\$		Ⓔ	1	102	Warm White			
T12 6" Spacing Watt-Miser®																					
T12	Medium Bi-Pin (G13)	35	22.5	12203	F35CW/U/6/WM	12	14000	2300	2100	4100	60		\$		Ⓔ	1	102				
		35	22.5	14471	F35CW/U/6/WM/UPC	12	14000	2300	2100	4100	60		\$		Ⓔ	1	102				
		35	22.5	23383	F35CW/U/6/WM/C	6	14000	2300	2100	4100	60		\$		Ⓔ	1	102				
		35	22.5	12207	F35WW/U/6/WM	12	14000	2350	2150	3000	52		\$		Ⓔ	1	102	Warm White			
T12 6" Spacing Watt-Miser® Ecolux®																					
T12	Medium Bi-Pin (G13)	35	22.5	15622	F35CW/U/6/WM/ECO	12	18000	2600	2235	4100	62		\$		Ⓔ	1	102				
T12 Instant Start																					
T12	Single Pin (Fa8)	20	24.0	10691	F24T12/CW	24	7500	1050	900	4100	60							101			
		30	36.0 cm	10709	F36T12/CW	24	7500	2000	1800	4100	60								101		
		35	42.0	10735	F42T12/CW	24	7500	2400	2210	4100	60								101		
		40	48.0	15262	F48T12/SP35	24	9000	3000	2820	3500	73									101	
		40	48.0	15088	F48T12/SPX30	24	9000	3050	2870	3000	82									101	
		40	48.0	15116	F48T12/SPX35	24	9000	3050	2870	3500	82									101	
		40	48.0	10748	F48T12/CW	24	9000	2875	2650	4100	60									101	
		40	48.0	20461	F48T12CW/UPC 6PK	24	9000	2875	2650	4100	60										101
Watt-Miser® Energy Saving Lamps																					
T12	Single Pin (Fa8)	30	48.0	14319	F48T12/SP35/WM	24	9000	2575	2420	3500	73		\$				1	101			
		30	48.0	13048	F48T12/SP41/WM	24	9000	2575	2420	4100	72		\$				1	101			
		30	48.0	44967	F48T12/CW/WM	24	9000	2475	2400	4100	60		\$				1	101			
8' T12 Instant Start																					
8' Instant Start Standard																					
T12	Single Pin (Fa8)	75	96.0	15357	F96T12SP30 15PK	15	12000	6500	6110	3000	70					Ⓔ		101			
		75	96.0	14067	F96T12SP35 15PK	15	12000	6500	6110	3500	73					Ⓔ		101			
		75	96.0	15358	F96T12/SP41 15PK	15	12000	6500	6110	4100	72					Ⓔ		101			
		75	96.0	12127	F96T12/SP65	15	12000	6125	5760	6500	75					Ⓔ		101			
		75	96.0	15110	F96T12SPX30 15PK	15	12000	6800	6390	3000	82					Ⓔ		101			
		75	96.0	15101	F96T12SPX35 15PK	15	12000	6800	6390	3500	82					Ⓔ		101			
		75	96.0	15335	F96T12SPX41 15PK	15	12000	6800	6390	4100	80					Ⓔ		101			
		75	96.0	23466	F96T12/SPX50	15	12000	6250	5880	5000	80					Ⓔ		101			
		75	96.0	14652	F96T12/DX	15	12000	4500	4050	6500	84					Ⓔ		101	Daylight Deluxe		