




ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1615 North Hazel St.
71801-0000, AR Hope
Phone: 870-777-4225
Fax: 870-777-4343



F44G90E 4X4 90D N1 Wway Elb

Hoffman Enclosures, Inc.

Catalog Number	F44G90E
Manufacturer	Hoffman Enclosures, Inc.
Description	Elbow 90-Degree Lay-In Wireway, 4.00X4.00, Gray, Mild Steel
Weight per unit	2.0 (lbs/each)
Product Category	Nema Type 1 Wireway & Fittings

Features

ip rating	IP30
Material	Mild Steel;Steel

Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Painted;Powder Coat

Dimensions and Weight

Height	4
Width	4

Descriptions

Description	4X4 90D N1 WWAY ELB
extra long description	NVENT HOF F44G90E 90 Elbow
Features	Lay-in Painted 90-Degree Elbows have all removable sides, retaining lay-in feature regardless of how the elbow is oriented. Lay-in feature allows wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system. Sides are held together with screws.
Long Description	Elbow 90-Degree Lay-in Wireway, 4.00x4.00, Gray, Mild Steel
Product Type	90 Elbow
Short Description	90 Elbow

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510525200
Manufacturers Part Number	F44G90E
UPC	783510525200

Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	Commercial Lay-in Hinged-Cover Type 1 Wireway;Elbow



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1615 North Hazel St.
71801-0000, AR Hope
Phone: 870-777-4225
Fax: 870-777-4343

Packaging

Carton	1
Package	4
Weight Per each	2

Uses, Certifications, and Standards

Application	Power Distribution
nema rating	1 Indoor, electrical protection