



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## F44LE45A 4X4 45D N12 Top Open Elb

Hoffman Enclosures, Inc.

Catalog Number	F44LE45A
Manufacturer	Hoffman Enclosures, Inc.
Description	Elbow 45-Degree Top Opening, 4.00X4.00, Gray, Steel
Weight per unit	3.3 (lbs/each)
Product Category	20200714082358

### Features

ip rating	IP54
Material	MILD STEEL

### Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Galvanized

### Dimensions and Weight

Height	4
Width	4

### Descriptions

Description	4X4 45D N12 TOP OPEN ELB
extra long description	NVENT HOF F44LE45A 45 Elbow, top o
Features	Lay-in Hinged-Cover 45-Degree Elbows are used for continuous wireway runs with 45-degree turns. Because sections of lay-in wireway can be mounted with covers oriented in any direction, three different 45-degree elbows are available. Proper selection allows the user to maintain the same access and thereby preserve the lay-in feature for right-angle installations.
Long Description	Elbow 45-Degree Top Opening, 4.00x4.00, Gray, Steel
Product Type	45 Elbow, Top Open

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510183707
Manufacturers Part Number	F44LE45A
UPC	783510183707

### Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	ELBOW

### Packaging

Carton	1
Weight Per each	3.3



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Application .....

nema rating .....

Power Distribution .....

12 Indoor, dust-resistant .....