



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1461 Technology Pkwy  
30165-0000, GA Rome  
Phone: 706-622-4953  
Fax: 706-622-4954



## F48T12CW 40W T12 48" 4100K Single Pin 62 Cri Fluor

*Sylvania-Ledvance*

Catalog Number	F48T12CW
Manufacturer	Sylvania-Ledvance
Description	39W, 48" Mol, T12 Instant Start Slimline Fluorescent Lamp, Cool White Phosphor, 4200K Color Temperature, 60 Cri
Weight per unit	0.6800 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

amperage rating	Ballast Dependent
average life	9000
Base	Single Pin
bulb type	T12
lumens	2820 Initial Lumens at 25 Degrees C
Shape	T12
start type	Instant Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	39

### Material, Color, and Finish

color rendering index (cri)	60
color temperature	4200
Finish	Phosphor Coated

### Dimensions and Weight

Diameter	1.5 in
----------	--------

### Descriptions

Description	40W T12 48" 4100K SINGLE PIN 62 CRI FLUOR
extra long description	SYL F48T12/CW/24830 F48T12CW 30/CS
Long Description	39W, 48" MOL, T12 instant start Slimline fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI
Product Type	F48T12CW 30/CS 1/Sku
Special Features	COOL WHITE



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1461 Technology Pkwy  
30165-0000, GA Rome  
Phone: 706-622-4953  
Fax: 706-622-4954

## Manufacturer Information

Brand	SYLVANIA
GTIN	00046135248306
Manufacturers Part Number	F48T12/CW/24830
UPC	046135248306

## Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

## Packaging

Carton	1
Package	30
Weight Per each	0.68

## Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------