



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3101 Industrial Terrace  
78758-0000, TX Austin  
Phone: 512-351-3290  
Fax: 512-973-9027



## F48T12CWH0 60W T12 48" Cool White High Output 62 Cri R17D

*Ge By Current Lamps*

Catalog Number	F48T12CWH0
Manufacturer	Ge By Current Lamps
Description	Fluorescent Lamp, Recessed Double Contact R17D Base, T12 Bulb Shape, 60, 20000 H Average Life, 4100 K, Cool White, 60 W, 3825 LM Brightness (Lumens), Soda Lime Housing Material, 1.5 In Diameter, 48.0 In Length, Rapid, 0.68 LB/Ea
Weight per unit	1.0 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

Base	Recessed Double Contact (R17d)
lumens	3825
Wattage	60

### Material, Color, and Finish

color rendering index (cri)	60.0
-----------------------------	------

### Dimensions and Weight

Diameter	1.5
Length	48

### Descriptions

Description	60W T12 48" COOL WHITE HIGH OUTPUT 62 CRI R17D
extra long description	GEL F48T12/CW/HO 10773 FLUORESCENT

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168107730
UPC	043168107730

### Taxonomies, Classifications, and Categories

Category Description	HIGH VOLUME FLUORESCENTS
----------------------	--------------------------

### Packaging

Carton	1
Package	24
Weight Per each	1.01