



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F48T12CWH0 60W T12 48" Cool White High Output 62 Cri R17D

Ge By Current Lamps

Catalog Number	F48T12CWH0
Manufacturer	Ge By Current Lamps
Description	Fluorescent Lamp, Recessed Double Contact R17D Base, T12 Bulb Shape, 60, 20000 H Average Life, 4100 K, Cool White, 60 W, 3825 LM Brightness (Lumens), Soda Lime Housing Material, 1.5 In Diameter, 48.0 In Length, Rapid, 0.68 LB/Ea
Weight per unit	1.0 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

Base	Recessed Double Contact (R17d)
lumens	3825.0
Wattage	60.0

Material, Color, and Finish

color rendering index (cri)	60.0
-----------------------------	------

Dimensions and Weight

Diameter	1.5
Length	48.0

Descriptions

Description	60W T12 48" COOL WHITE HIGH OUTPUT 62 CRI R17D
extra long description	GEL F48T12/CW/HO 10773 FLUORESCENT

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168107730
UPC	043168107730

Taxonomies, Classifications, and Categories

Category Description	HIGH VOLUME FLUORESCENTS
----------------------	--------------------------

Packaging

Carton	1
Package	24
Weight Per each	1.01