



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1910 Business Interstate 35E
78061-0000, TX Pearsall
Phone: 830-334-5353
Fax: 830-334-5757



F48T12DH0 60W T12 48" Daylight High Output 76 Cri R17D

Ge By Current Lamps

Catalog Number	F48T12DH0
Manufacturer	Ge By Current Lamps
Description	Ge, 60 WTT, 3400 LM, 6500 KV, 75 Cri, 1.5 In Diameter, 48 In Length, Recessed Double Contact (R17D) Base, 12000 HR Average Life
Weight per unit	0.8300 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

average life	12000
Base	Recessed Double Contact (R17d)
lumens	3400
Wattage	60

Material, Color, and Finish

color rendering index (cri)	75.0
color temperature	6500.0

Dimensions and Weight

Diameter	1.5
Length	48

Descriptions

Description	60W T12 48" DAYLIGHT HIGH OUTPUT 76 CRI R17D
extra long description	GEL F48T12/D/HO 10778 FLUORESCENT
Long Description	GE, 60 WTT, 3400 LM, 6500 KV, 75 CRI, 1.5 IN Diameter, 48 IN Length, Recessed Double Contact (R17d) Base, 12000 HR Average Life
Product Type	10778 Fluorescent

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168107785
Manufacturers Part Number	F48T12/D/HO
UPC	043168107785

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Packaging

Carton	1
Package	24
Weight Per each	0.83



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1910 Business Interstate 35E
78061-0000, TX Pearsall
Phone: 830-334-5353
Fax: 830-334-5757

Uses, Certifications, and Standards

Application Full Wattage