



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1308 North Nelson Street  
79735-0000, TX Fort Stockton  
Phone: 432-336-8730  
Fax: 432-336-3279



## F48T12DH0 60W T12 48" Daylight High Output 76 Cri R17D

*Ge By Current Lamps*

Catalog Number	F48T12DH0
Manufacturer	Ge By Current Lamps
Description	Ge, 60 WTT, 3400 LM, 6500 KV, 75 Cri, 1.5 In Diameter, 48 In Length, Recessed Double Contact (R17D) Base, 12000 HR Average Life
Weight per unit	0.8300 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

average life	12000
Base	Recessed Double Contact (R17d)
lumens	3400
Wattage	60

### Material, Color, and Finish

color rendering index (cri)	75.0
color temperature	6500.0

### Dimensions and Weight

Diameter	1.5
Length	48

### Descriptions

Description	60W T12 48" DAYLIGHT HIGH OUTPUT 76 CRI R17D
extra long description	GEL F48T12/D/HO 10778 FLUORESCENT
Long Description	GE, 60 WTT, 3400 LM, 6500 KV, 75 CRI, 1.5 IN Diameter, 48 IN Length, Recessed Double Contact (R17d) Base, 12000 HR Average Life
Product Type	10778 Fluorescent

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168107785
Manufacturers Part Number	F48T12/D/HO
UPC	043168107785

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

### Packaging

Carton	1
Package	24
Weight Per each	0.83



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1308 North Nelson Street  
79735-0000, TX Fort Stockton  
Phone: 432-336-8730  
Fax: 432-336-3279

---

## Uses, Certifications, and Standards

Application .....

Full Wattage .....