



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F60T12CWH0 75W T12 60" Cool White High Output 62 Cri R17D

Ge By Current Lamps

Catalog Number	F60T12CWH0
Manufacturer	Ge By Current Lamps
Description	Fluorescent Lamp, Recessed Double Contact R17D Base, T12 Bulb Shape, 60, 12000 H Average Life, 4100 K, Cool White, 75 W, 5150 LM Brightness (Lumens), Soda Lime Housing Material, 1.5 In Diameter, 60.0 In Length, Rapid, -29 °C Operating Temperature, 1.34 LB/Ea
Weight per unit	0.8400 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

Base	Recessed Double Contact (R17d)
lumens	5150
Wattage	75

Material, Color, and Finish

color rendering index (cri)	60.0
-----------------------------	------

Dimensions and Weight

Diameter	1.5
----------	-----

Descriptions

Description	75W T12 60" COOL WHITE HIGH OUTPUT 62 CRI R17D
extra long description	GEL F60T12/CWHO-15PK 23075 FLUORE

Manufacturer Information

Brand	GE Current
GTIN	00043168230759
Manufacturers Part Number	F60T12/CWHO 15PK
UPC	043168230759

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Packaging

Carton	1
Package	15
Weight Per each	0.84