



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

7520 Eastgate Blvd Suite 100
37122-0000, TN Mt. Juliet
Phone: 615-257-4146
Fax: 615-257-4147



F60T12DH0 75W T12 60" Daylight High Output 76 Cri R17D

Ge By Current Lamps

Catalog Number	F60T12DH0
Manufacturer	Ge By Current Lamps
Description	Fluorescent Lamp, Recessed Double Contact R17D Base, T12 Bulb Shape, 75, 12000 H Average Life, 6500 K, 75 W, 4400 LM Brightness (Lumens), Soda Lime Housing Material, 1.5 In Diameter, 60.0 In Length, Rapid, -29 °C Operating Temperature, 0.87 LB/Ea
Weight per unit	0.8400 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

Base	Recessed Double Contact (R17d)
lumens	4400
Wattage	75

Material, Color, and Finish

color rendering index (cri)	75.0
-----------------------------	------

Dimensions and Weight

Diameter	1.5
----------	-----

Descriptions

Description	75W T12 60" DAYLIGHT HIGH OUTPUT 76 CRI R17D
extra long description	GEL F60T12/D/HO-15PK 23077 FLUORE

Manufacturer Information

Brand	GE Current, a Daintree company
GTIN	00043168230773
Manufacturers Part Number	F60T12/D/HO 15PK
UPC	043168230773

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Packaging

Carton	1
Package	15
Weight Per each	0.84