



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2108 South Huber  
79007-0000, TX Borger  
Phone: 806-273-3085  
Fax: 806-273-2487



## F66G24WK 6X6X24 N1 HC STRT SCT

*Hoffman Enclosures, Inc.*

Catalog Number	F66G24WK
Manufacturer	Hoffman Enclosures, Inc.
Description	Lay-In Wireway, Gray, Polyester Powder Paint, Steel, Hinged Cover, 6 In Overall Height, 24 In Overall Length, 6 In Overall Width, 46 LB
Weight per unit	46.0 (lbs/each)
Product Category	Nema Type 1 Wireway & Fittings

### Features

ip rating	IP30
-----------	------

### Material, Color, and Finish

Color Code	ANSI 61
Style	Liftoff Cover with Knockouts

### Dimensions and Weight

Height	6
Width	6

### Descriptions

Description	6X6X24 N1 HC STRT SCT
extra long description	NVENT HOF F66G24WK 24.00in Straight
Features	Lay-in Hinged-Cover Type 1 Straight Sections are used for enclosing wire and cable in wireway runs. Sections are completely open on one side so wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system. Sections are available in lengths from 12 inch to 120 inch, with or without knockouts.

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510529604
UPC	783510529604

### Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	Commercial Lay-in Hinged-Cover Type 1 Wireway;Straight Section

### Packaging

Carton	1
Weight Per each	46



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2108 South Huber  
79007-0000, TX Borger  
Phone: 806-273-3085  
Fax: 806-273-2487

---

## Uses, Certifications, and Standards

Application .....	Power Distribution .....
nema rating .....	1 .....