



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1461 Technology Pkwy
30165-0000, GA Rome
Phone: 706-622-4953
Fax: 706-622-4954



F66G60 6X6X60 N1 HC STRT SCT

Hoffman Enclosures, Inc.

Catalog Number	F66G60
Manufacturer	Hoffman Enclosures, Inc.
Description	Straight Section Lay-In Hinged-Cover Type 1 No Kos, 6X6X60, Gray, Steel
Weight per unit	53.0 (lbs/each)
Product Category	Nema Type 1 Wireway & Fittings

Features

ip rating	IP30
Knockouts	FALSE
Material	Mild Steel;Steel

Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Painted;Powder Coat
Style	Liftoff Cover no Knockouts

Dimensions and Weight

Height	6
Width	6

Descriptions

Description	6X6X60 N1 HC STRT SCT
extra long description	NVENT HOF F66G60 60.00in Straight S
Features	Lay-in Hinged-Cover Type 1 Straight Sections are used for enclosing wire and cable in wireway runs. Sections are completely open on one side so wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system. Sections are available in lengths from 12 inch to 120 inch, with or without knockouts.
Long Description	Straight Section Lay-in Hinged-Cover Type 1 no KOs, 6x6x60, Gray, Steel
Product Type	60.00IN Straight Section
Short Description	60.00in Straight Section

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510523800
Manufacturers Part Number	F66G60
UPC	783510523800



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1461 Technology Pkwy
30165-0000, GA Rome
Phone: 706-622-4953
Fax: 706-622-4954

Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	Commercial Lay-in Hinged-Cover Type 1 Wireway;Straight Section

Packaging

Carton	1
Package	2
Weight Per each	53

Uses, Certifications, and Standards

Application	Power Distribution
nema rating	1