



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

6510 Broadway St  
77554-0000, TX Galveston  
Phone: 409-741-0072  
Fax: 409-741-0433



## F72T12CWH0 85W T12 72" Cool White High Output 62 Cri R17D

*Ge By Current Lamps*

Catalog Number	F72T12CWH0
Manufacturer	Ge By Current Lamps
Description	Fluorescent Lamp, Recessed Double Contact R17D Base, T12 Bulb Shape, 60, 12000 H Average Life, 4100 K, Cool White, 85 W, 6350 LM Brightness (Lumens), Soda Lime Housing Material, 1.5 In Diameter, 72.0 In Length, Rapid, -29 °C Operating Temperature, 1.07 LB/Ea
Weight per unit	1.3 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

Base	Recessed Double Contact (R17d)
lumens	6350
Wattage	85

### Material, Color, and Finish

color rendering index (cri)	60.0
-----------------------------	------

### Dimensions and Weight

Diameter	1.5
----------	-----

### Descriptions

Description	85W T12 72" COOL WHITE HIGH OUTPUT 62 CRI R17D
extra long description	GEL F72T12CW/HO-15PK 13697 FLUORE

### Manufacturer Information

Brand	GE Current
GTIN	00043168136976
Manufacturers Part Number	F72T12CW/HO 15PK
UPC	043168136976

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

### Packaging

Carton	1
Package	15
Weight Per each	1.31