



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1500 West Cotton
75604-0000, TX Longview
Phone: 903-757-8491
Fax: 903-758-0441



F72T12CWH0 85W T12 72" Cool White High Output 62 Cri R17D

Ge By Current Lamps

Catalog Number	F72T12CWH0
Manufacturer	Ge By Current Lamps
Description	Fluorescent Lamp, Recessed Double Contact R17D Base, T12 Bulb Shape, 60, 12000 H Average Life, 4100 K, Cool White, 85 W, 6350 LM Brightness (Lumens), Soda Lime Housing Material, 1.5 In Diameter, 72.0 In Length, Rapid, -29 °C Operating Temperature, 1.07 LB/Ea
Weight per unit	1.3 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

Base	Recessed Double Contact (R17d)
lumens	6350
Wattage	85

Material, Color, and Finish

color rendering index (cri)	60.0
-----------------------------	------

Dimensions and Weight

Diameter	1.5
----------	-----

Descriptions

Description	85W T12 72" COOL WHITE HIGH OUTPUT 62 CRI R17D
extra long description	GEL F72T12CW/HO-15PK 13697 FLUORE

Manufacturer Information

Brand	GE Current
GTIN	00043168136976
Manufacturers Part Number	F72T12CW/HO 15PK
UPC	043168136976

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Packaging

Carton	1
Package	15
Weight Per each	1.31