



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

711 Lake Bardwell Dr.  
75119-0000, TX Ennis  
Phone: 972-875-3413  
Fax: 972-875-3174



## F72T12DH0 85W T12 72" Daylight High Output 76 Cri R17D

*Ge By Current Lamps*

Catalog Number	F72T12DH0
Manufacturer	Ge By Current Lamps
Description	Fluorescent Lamp, Recessed Double Contact R17D Base, T12 Bulb Shape, 75, 12000 H Average Life, 6500 K, 85 W, 5350 LM Brightness (Lumens), Soda Lime Housing Material, 1.5 In Diameter, 72.0 In Length, Rapid, -29 °C Operating Temperature, 1.35 LB/Ea
Weight per unit	1.4 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

Base	Recessed Double Contact (R17d)
lumens	5350
Wattage	85

### Material, Color, and Finish

color rendering index (cri)	75.0
-----------------------------	------

### Dimensions and Weight

Diameter	1.5
----------	-----

### Descriptions

Description	85W T12 72" DAYLIGHT HIGH OUTPUT 76 CRI R17D
extra long description	GEL F72T12D/HO-15PK 13699 FLUORES

### Manufacturer Information

Brand	GE Current, a Daintree company
GTIN	00043168136990
Manufacturers Part Number	F72T12D/HO 15PK
UPC	043168136990

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

### Packaging

Carton	1
Package	15
Weight Per each	1.35