



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3520 S Sam Houston Pkwy East Suite 900
77047-0000, TX Houston
Phone: 281-412-7049
Fax: 281-412-7314

F72T12DH0 85W T12 72" Daylight High Output 76 Cri R17D

Sylvania-Ledvance

Catalog Number	F72T12DH0
Manufacturer	Sylvania-Ledvance
Description	85W, 72"Mol, T12 Ho (800 Ma) Rapid Start Fluorescent Lamp, Daylightphosphor, 6500K Color Temperature, 72 Cri
Weight per unit	1.1 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Recessed Double Contact
bulb type	T12
lumens	5550 Initial Lumens at 25 Degrees C
Shape	T12
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	85

Material, Color, and Finish

color rendering index (cri)	76
color temperature	6500

Descriptions

Description	85W T12 72" DAYLIGHT HIGH OUTPUT 76 CRI R17D
extra long description	SYL F72T12/D/HO/25189 F72T12DHO 15/
Long Description	85W, 72"MOL, T12 HO (800 mA) rapid start fluorescent lamp, Daylightphosphor, 6500K color temperature, 72 CRI

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135251894
Manufacturers Part Number	F72T12/D/HO/25189
UPC	046135251894

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	15
Weight Per each	1.08

Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------