


### 10829 - F72T8/CW

GE Cool White Starcoat® T8



### **CAUTIONS & WARNINGS**

#### Caution


- · Lamp may shatter and cause injury if broken
- Wear safety glasses and gloves when handling lamp.
- Do not use excessive force when installing lamp.

#### Warning

- · Risk of Electric Shock
- Turn power off before inspection, installation or removal.

### **GRAPHS & CHARTS**

**Graphs\_Spectral Power Distribution** 



### **Graphs\_Lamp Mortality**



### **NOTES**

• Not for sale for use in OR

# **GENERAL CHARACTERISTICS**

Linear Fluorescent - Straight Lamp Type

Linear

Bulb T8

Single Pin (Fa8) Base Rated Life 7500.0 hrs **Bulb Material** Soda lime Starting Temperature (MIN) 10.0 °C

LEED-EB MR Credit 4396 picograms Hg per

mean lumen hour

**Primary Application** Full Wattage

### PHOTOMETRIC CHARACTERISTICS

**Initial Lumens** 3000.0 Mean Lumens 2730.0 Nominal Initial Lumens per Watt 85 Color Temperature 4100.0 K Color Rendering Index (CRI) 60.0

### **ELECTRICAL CHARACTERISTICS**

Wattage Voltage 220.0

Open Circuit Voltage (instant 540 V @ 10 °C

start ) Min @ Temperature

Cathode Resistance Ratio - Rh/ 4.25

Rc (MIN)

Cathode Resistance Ratio - Rh/ 6.5

Rc (MAX)

Current Crest Factor (MAX) 1.7

### **DIMENSIONS**

Maximum Overall Length 72.0000 in(1828.8 mm)

(MOL)

Minimum Overall Length 69.7400 in(1771.4 mm) Nominal Length 72.000 in(1828.8 mm) Bulb Diameter (DIA) (MIN) 0.940 in(23.9 mm) Bulb Diameter (DIA) (MAX) 1.100 in(27.9 mm) Bulb Diameter (DIA) 1.000 in(25.4 mm) Max Base Face to Base Face 69.300 in(1760.2 mm)

(A)

Face to End of Opposing Pin 69.420 in(1763.3 mm)

(B) (MIN)

Face to End of Opposing Pin 69.650 in(1769.1 mm)

(B) (MAX)

End of Base Pin to End of 69.740 in(1771.4 mm)

Opposite Pin End (C)

## PRODUCT INFORMATION

**Product Code** 10829 Description F72T8/CW ANSI Code 3010-1 Standard Package Case

Standard Package GTIN 10043168108291

Standard Package Quantity 24 Sales Unit Unit No Of Items Per Sales Unit No Of Items Per Standard 24

Package

UPC 043168108294