



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **F8718C 1-1/0AWG SNGL Wire Bare Ferrule** *Panduit Corporation*

|                  |                                                                  |
|------------------|------------------------------------------------------------------|
| Catalog Number   | F8718C                                                           |
| Manufacturer     | Panduit Corporation                                              |
| Description      | Ferrule, Non-Covered, 1-1/0 Awg Wire Range, 0.71(18.0MM) Length. |
| Weight per unit  | 0.0040 (lbs/each)                                                |
| Product Category | Large Terminals & Connectors                                     |

### **Features**

|            |               |
|------------|---------------|
| insulation | Non-Insulated |
| Material   | Copper        |
| Wire Size  | 1/0           |

### **Material, Color, and Finish**

|        |          |
|--------|----------|
| Color  | Metallic |
| Finish | Tinned   |

### **Descriptions**

|                        |                                                                  |
|------------------------|------------------------------------------------------------------|
| Description            | 1-1/0AWG SNGL WIRE BARE FERRULE                                  |
| extra long description | PAN F87-18-C Pan-Term® F87-18-C Non                              |
| Long Description       | Ferrule, Non-Covered, 1-1/0 AWG wire range, 0.71(18.0mm) length. |
| Product Type           | Pan-Term® F87-18-C Non-Covered Ferrules                          |

### **Manufacturer Information**

|                           |                |
|---------------------------|----------------|
| Brand                     | Panduit®       |
| GTIN                      | 00074983763719 |
| Manufacturers Part Number | F87-18-C       |
| UPC                       | 074983763719   |

### **Taxonomies, Classifications, and Categories**

|      |                     |
|------|---------------------|
| Type | Non-Covered Ferrule |
|------|---------------------|

### **Availability**

|             |     |
|-------------|-----|
| minimum qty | 100 |
|-------------|-----|

### **Packaging**

|                 |       |
|-----------------|-------|
| Carton          | 100   |
| Weight Per each | 0.004 |

### **Uses, Certifications, and Standards**

|                    |                                                      |
|--------------------|------------------------------------------------------|
| Mounting           | 23/32                                                |
| standard           | DIN 46228, CSA C22.2 No. 291-14, UL 486F, cULus 486F |
| Temperature Rating | 302 Degrees Fahrenheit (150 Degrees Celsius)         |