



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5510 West 65th Street  
72209-0000, AR Little Rock  
Phone: 501-565-1785  
Fax: 501-565-0827



## F88G12 8X8X12 N1 HC STRT SCT

*Hoffman Enclosures, Inc.*

Catalog Number	F88G12
Manufacturer	Hoffman Enclosures, Inc.
Description	Straight Section Lay-In Hinged-Cover Type 1 No Kos, 8X8X12, Gray, Steel
Weight per unit	9.0 (lbs/each)
Product Category	Nema Type 1 Wireway & Fittings

### Features

ip rating	IP30
Knockouts	FALSE
Material	Mild Steel;Steel

### Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Painted;Powder Coat
Style	Liftoff Cover no Knockouts

### Dimensions and Weight

Height	8
Width	8

### Descriptions

Description	8X8X12 N1 HC STRT SCT
extra long description	NVENT HOF F88G12 12.00in Straight S
Features	Lay-in Hinged-Cover Type 1 Straight Sections are used for enclosing wire and cable in wireway runs. Sections are completely open on one side so wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system. Sections are available in lengths from 12 inch to 120 inch, with or without knockouts.
Long Description	Straight Section Lay-in Hinged-Cover Type 1 no KOs, 8x8x12, Gray, Steel
Product Type	12.00IN Straight Section
Short Description	12.00in Straight Section

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510526009
Manufacturers Part Number	F88G12
UPC	783510526009



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5510 West 65th Street  
72209-0000, AR Little Rock  
Phone: 501-565-1785  
Fax: 501-565-0827

## Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	Commercial Lay-in Hinged-Cover Type 1 Wireway;Straight Section

## Packaging

Carton	1
Weight Per each	9

## Uses, Certifications, and Standards

Application	Power Distribution
nema rating	1